



Powering Business Worldwide

pe.eaton.com

Photoelectric Sensor

14101ASQD05

UPC:782114414897

Dimensions:

- **Height:** .71 IN
- **Length:** 2.2 IN
- **Width:** .47 IN

Warranties:

- 3 year

Specifications:

- **Connection:** Dual key micro
- **Contact Rating:** 300 mA AC/DC at 20-264 Vac/15-30 Vdc
- **Contact Configuration:** AC: L1 switched, DC: NPN open collector
- **Enclosure Material:** Polyurethane Foam (RIM)
- **Environmental Rating:** NEMA 1, 3, 4, 4X, 6, 12, 13, IP69k
- **Input Voltage:** 90-132 Vac 50/60 Hz, 18-50 Vdc
- **Led Indicators:** Output ON
- **Maximum Ac Current:** 300 mA
- **Number Of Pins:** 3 pin
- **Operating Temperature:** -40° to 158°F (-40° to 70°C)
- **Protection:** Auto reset
- **Sensor Type:** Polarized Retroreflective

Supporting documents:

- [Comet series - Photoelectric sensors](#)
- [Eatons Volume 8-Sensing Solutions](#)
- [Eaton Specification Sheet - 14101ASQD05](#)

Certifications:

- UL Recognized
- cUL Recognized



Product compliance: No Data

© 2016 Eaton. All rights reserved.