



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type FB Tri-Pac Thermal-Magnetic Circuit Breaker

**FB3070PL**

**UPC:**786679765531

### Dimensions:

- **Height:** 4.125 IN
- **Length:** 8.75 IN
- **Width:** 3.5 IN

**Weight:**11.5 LB

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Amperage Rating:** 70A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 100 kAIC at 250 Vdc
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 600 Vac, 250 Vdc
- **Accessories:** Replaceable current limiter
- **Terminals:** Line and load

### Supporting documents:

- [Miniature and Molded Case Circuit Breakers](#)
- [Eaton Specification Sheet - FB3070PL](#)

### Certifications:

- UL 489

**Product compliance:** No Data

