

Product Selection

Plug-On Circuit Breakers, Types BR—10/22/42 kAIC, 120 Vac, 120/240 Vac and 240 Vac

BR120



BR215



BR320



BRH2100



Type BR Breakers, 1-Inch (25.4 mm) per Pole 120/240, 10, 22 and 42 kAIC

Ampere Rating	Wire Size Range Cu/Al 60°C or 75°C	Single-Pole 120/240 Vac Requires One 1-Inch (25.4 mm) Space 10 per Shelf Carton		Two-Pole 120/240 Vac Common Trip Requires Two 1-Inch (25.4 mm) Spaces 5 per Shelf Carton		42 kAIC Catalog Number
		10 kAIC Catalog Number	22 kAIC Catalog Number	10 kAIC Catalog Number	22 kAIC Catalog Number	
10	#14-4	BR110	—	BR210	—	—
15	#14-4	BR115 ^{①②}	BRH115	BR215 ^③	BRH215	—
20	#14-4	BR120 ^{①②}	BRH120	BR220 ^③	BRH220	—
25	#14-4	BR125	BRH125	BR225 ^③	BRH225	—
30	#14-4	BR130	BRH130	BR230 ^③	BRH230	—
35	#14-4	BR135	BRH135	BR235 ^③	BRH235	—
40	#14-4	BR140	BRH140	BR240 ^③	BRH240 ^③	—
45	#14-4	—	BRH145	BR245 ^③	BRH245	—
50	#14-4	BR150	BRH150	BR250 ^③	BRH250 ^③	—
55	#14-3	BR150	BRH155	BR255	BRH255	—
60	#8-1/0	BR160	BRH160	BR260	BRH260	BRHH260
70	#8-1/0	BR170	BRH170	BR270	BRH270	BRHH270
80	#8-1/0	—	—	BR280	BRH280	BRHH280
90	#8-1/0	—	—	BR290	BRH290	BRHH290
100	#8-1/0	—	—	BR2100	BRH2100	BRHH2100
110	#8-1/0	—	—	BR2110	BRH2110	BRHH2110
125	#4-2/0	—	—	BR2125	BRH2125	BRHH2125
150	#4-2/0	—	—	BR2150 ^④	—	—



Notes

- ① One pole, 1-inch (25.4 mm) per pole circuit breakers are available with high magnetic setting for switching large tungsten lamp loads. Add suffix H to catalog number.
 - ② Switching duty rated.
 - ③ On the black handle breaker, add suffix "B" to the catalog number to obtain a tapped molded opening for proper use with hold-down kits.
 - ④ For use as a branch circuit breaker in 400 and 600 ampere panels only.
- All Type BR single-, two- and three-pole circuit breakers carry listing for HACR application. For circuit breakers with a shunt trip, add ST suffix.