

Group Metering — Main Tenant Circuit Breakers

35MM, 37MM, 35SS, and 37SS
Main Tenant Circuit Breakers

- The following breakers are to be used on 35MM, 37MM, 35SS, and 37SS modular metering stacks.
- Series rating information available on Pages 5-39 through 5-41.
- 2-pole breakers are 120/240V AC
 - field installed.
- 3-pole breakers are 208Y/120V AC
 - field installed.



CC2200



EHD2100

Table 5-30. 35MM, 37MM, 35SS, and 37SS Main Tenant Circuit Breakers

Description	Number of Poles	Main Tenant Circuit Breaker Ampere Rating	10,000 AIC		25,000 AIC		42,000 AIC		100,000 AIC	
			Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$	Catalog Number	Price U.S. \$
Bolt-on type circuit breakers used with 35MM and 35SS (single-phase modular metering stacks) ②	2	15	EHD2015 ①	387.	—	—	—	—	—	—
	2	20	EHD2020 ①	387.	—	—	—	—	—	—
	2	30	EHD2030 ①	387.	—	—	—	—	—	—
	2	40	EHD2040 ①	387.	—	—	—	—	—	—
	2	50	EHD2050 ①	387.	—	—	—	—	—	—
	2	60	EHD2060 ①	387.	CHH2060H2X	670.	CHH2060H4X	695.	CHH2060X	750.
	2	70	EHD2070 ①	505.	CHH2070H2X	670.	CHH2070H4X	695.	CHH2070X	750.
	2	80	EHD2080 ①	505.	CHH2080H2X	670.	CHH2080H4X	695.	CHH2080X	750.
	2	90	EHD2090 ①	505.	CHH2090H2X	670.	CHH2090H4X	695.	CHH2090X	750.
	2	100	CC2100X	304.	CHH2100H2X	670.	CHH2100H4X	695.	CHH2100X	750.
	2	125	CC2125X	304.	CHH2125H2X	670.	CHH2125H4X	695.	CHH2125X	750.
	2	150	CC2150X	304.	CHH2150H2X	670.	CHH2150H4X	695.	CHH2150X	750.
Bolt-on type circuit breakers used with 37MM and 37SS (three-phase modular metering stacks) ②	2	175	CC2175X	304.	CHH2175H2X	670.	CHH2175H4X	695.	CHH2175X	750.
	2	200	CC2200X	304.	CHH2200H2X	670.	CHH2200H4X	695.	CHH2200X	750.
	2	225	CC2225X	304.	CHH2225H2X	670.	CHH2225H4X	695.	CHH2225X	750.
	3	15	EHD3015 ①	498.	—	—	—	—	—	—
	3	20	EHD3020 ①	498.	—	—	—	—	—	—
	3	30	EHD3030 ①	498.	—	—	—	—	—	—
	3	40	EHD3040 ①	498.	—	—	—	—	—	—
	3	50	EHD3050 ①	498.	—	—	—	—	—	—
	3	60	EHD3060 ①	498.	CHH3060H2X	1,095.	CHH3060H4X	1,260.	CHH3060	1,125.
	3	70	EHD3070 ①	600.	CHH3070H2X	1,095.	CHH3070H4X	1,260.	CHH3070	1,125.
	3	80	EHD3080 ①	600.	CHH3080H2X	1,095.	CHH3080H4X	1,260.	CHH3080	1,125.
	3	90	EHD3090 ①	600.	CHH3090H2X	1,095.	CHH3090H4X	1,260.	CHH3090	1,125.
	3	100	CC3100X	443.	CHH3100H2X	1,095.	CHH3100H4X	1,260.	CHH3100	1,125.
	3	125	CC3125X	443.	CHH3125H2X	1,095.	CHH3125H4X	1,260.	CHH3125	1,125.
	3	150	CC3150X	815.	CHH3150H2X	1,095.	CHH3150H4X	1,260.	CHH3150	1,125.
3	175	CC3175X	815.	CHH3175H2X	1,095.	CHH3175H4X	1,260.	CHH3175	1,125.	
3	200	CC3200X	815.	CHH3200H2X	1,095.	CHH3200H4X	1,260.	CHH3200	1,125.	
3	225	CC3225X	815.	CHH3225H2X	1,095.	CHH3225H4X	1,260.	CHH3225	1,125.	

① EHD main tenant circuit breakers require one 37MMCBK kit per breaker.
② Main tenant circuit breakers are also available in ratings from 15 to 50 amperes.