



Powering Business Worldwide

pe.eaton.com

22.5 mm, Non-metallic Heavy-Duty Pushbutton Operator

E22T2

UPC:782113469539

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Maximum of 2 contact blocks (4 circuits) when used with supplied 3-way adapter

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Extended
- **Actuator Color:** Red
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Illuminated
- **Light Unit Type:** No light unit
- **Operating Mode:** Momentary
- **Size:** 25 mm
- **Series:** E22

Supporting documents:

- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)
- [Eatons Volume 12-Aftermarket, Renewal Parts and Life Extension Solutions](#)
- [Eaton Specification Sheet - E22T2](#)

Certifications:



- UL 508
- CSA Certified
- IEC 947-5-1 MTTA
- Lloyd's Register Certified

Product compliance:

- CE Marked

© 2016 Eaton. All rights reserved.