



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 22.5 mm, Non-metallic Heavy-Duty Pushbutton Operator

**E22TB2X26**

**UPC:**782113642581

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**Maximum of 2 contact blocks (4 circuits) when used with supplied 3-way adapter

### Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Specifications:

- **Type:** 22.5 mm, Non-metallic Heavy-Duty
- **Actuator:** Extended
- **Actuator Color:** Red
- **Actuator Material:** Plastic
- **Bezel:** Black
- **Enclosure:** NEMA 3, 3R, 4, 4X, 12, 13
- **Illumination:** Illuminated
- **Lamp Voltage:** 60 Vac/dc
- **Led Lamp Number:** W1226
- **Light Unit Type:** Incandescent, resistor
- **Light Unit Voltage:** 120 Vac/dc
- **Operating Mode:** Momentary
- **Size:** 25 mm
- **Series:** E22

### Supporting documents:

- [Pushbuttons, Indicating lights, Selector switches and Stacklights](#)
- [Eaton Specification Sheet - E22TB2X26](#)



**Certifications:**

- CSA Certified
- UL 508
- IEC 947-5-1 MTTA
- Lloyd's Register Certified

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.