



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Class I Division 2 Assembled Control Station

E34EX7003P

UPC:782114524084

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:** Use NEMA 4X 10250T operators where exposed to ultraviolet light

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Class I Division 2
- **Actuator:** Pushbutton, flush
- **Actuator Color:** Green
- **Contact Configuration:** 1NO-1NC
- **Enclosure Material:** Polyester
- **Legend:** START
- **Number Of Elements:** 1
- **Operating Mode:** Momentary
- **Rating:** NEMA 4, 4X, 12, 13, NEC Class I Division 2, Groups B, C and D
- **Series:** E34

### Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

### Certifications:

- UL 505
- CSA Certified

### Product compliance:

- CE Marked



- FDA 3-A

---

© 2016 Eaton. All rights reserved.