



Powering Business Worldwide

pe.eaton.com

30.5 mm, Corrosion Resistant Watertight/Oiltight, Enclosure

E34F13

UPC:782113702551

Dimensions:

- **Height:** 4.1 IN
- **Length:** 7.9 IN
- **Width:** 4.5 IN

Weight: .65 LB

Notes: Use NEMA 4X 10250T operators where exposed to ultraviolet light. All cast enclosures can be converted to base mounting of contact blocks. When used with E30 Pushbuttons, only the one element enclosure can be used.

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Corrosion Resistant Watertight/Oiltight
- **Bus Material:** Die cast
- **Enclosure:** NEMA 4, 4X, 12, 13
- **Mounting:** Flush
- **Number Of Elements:** 3
- **Product Category:** Enclosure

Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

Certifications:

- UL 505
- CSA Certified

Product compliance:



- CE Marked
- FDA 3-A

© 2016 Eaton. All rights reserved.