



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Class I Division 2 Assembled Indicating Light

**E34FB197HLGG24**

**UPC:**782114546161

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:**Use NEMA 4X 10250T operators where exposed to ultraviolet light

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Class I Division 2  
Watertight/Oiltight
- **Actuator:** Standard
- **Light Unit Type:** LED, full voltage
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13, NEC Class  
I Division 2, Groups B, C and D
- **Lamp Voltage:** 24 Vac/dc
- **Led Lamp Number:** Bayonet base
- **Lens Color:** Green
- **Lens Material:** Glass
- **Series:** E34

### Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

### Certifications:

- UL 505
- CSA Certified

### Product compliance:

- CE Marked



- FDA 3-A

---

© 2016 Eaton. All rights reserved.