



Powering Business Worldwide

pe.eaton.com

30.5 mm, Class I Division 2 Assembled Indicating Light

E34FB197HLGP2A

UPC:782114546468

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Use NEMA 4X 10250T operators where exposed to ultraviolet light

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Class I Division 2
Watertight/Oiltight
- **Actuator:** Standard
- **Light Unit Type:** LED, full voltage
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13, NEC Class
I Division 2, Groups B, C and D
- **Lamp Voltage:** 120 Vac
- **Led Lamp Number:** Bayonet base
- **Lens Color:** Green
- **Lens Material:** Plastic
- **Series:** E34

Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

Certifications:

- UL 505
- CSA Certified

Product compliance:

- FDA 3-A



- CE Marked

© 2016 Eaton. All rights reserved.