



Powering Business Worldwide

pe.eaton.com

30.5 mm, Corrosion Resistant Assembled Indicating Light

E34FB197LRP24

UPC:782114722541

Dimensions:

- Height: X
- Length: X
- Width: X

Notes: Use NEMA 4X 10250T operators where exposed to ultraviolet light

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Corrosion Resistant Watertight/Oiltight
- **Actuator:** Standard
- **Light Unit Type:** LED, full voltage
- **Rating:** NEMA 3, 3R, 3S, 4, 4X, 12, 13
- **Lamp Voltage:** 24 Vac/dc
- **Led Lamp Number:** Bayonet base
- **Lens Color:** Red
- **Lens Material:** Plastic
- **Series:** E34

Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- FDA 3-A
- CE Marked



