



Powering Business Worldwide

pe.eaton.com

30.5 mm, Corrosion Resistant, Assembled Push-Pull Unit

E34GDB63M2-1X

UPC:782113791630

Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

Notes:Assembled at Factory

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Corrosion Resistant
- **Actuator:** Standard
- **Actuator Color:** Red
- **Bus Material:** Plastic
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Illuminated
- **Light Unit Type:** Incandescent, transformer
- **Light Unit Voltage:** 120 Vac
- **Number Of Positions:** Two-position
- **Operating Mode:** Maintained push and pull
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** E34

Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

Certifications:

- CSA Certified
- UL Listed



Product compliance:

- CE Marked
- FDA 3-A

© 2016 Eaton. All rights reserved.