



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Corrosion Resistant, Assembled Push-Pull Unit

**E34GDB97LRD2A-1X**

**UPC:**782114721049

### Dimensions:

- **Height:** 2.2 IN
- **Length:** 4.2 IN
- **Width:** 2.2 IN

**Weight:**.36 LB

**Notes:**Assembled at Factory

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Corrosion Resistant
- **Actuator:** Standard
- **Actuator Color:** Red
- **Bus Material:** Plastic
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Illuminated
- **Light Unit Type:** LED, full voltage
- **Light Unit Voltage:** 120 Vac/dc
- **Number Of Positions:** Two-position
- **Operating Mode:** Maintained push and pull
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** E34

### Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

### Certifications:

- CSA Certified



- UL Listed

**Product compliance:**

- FDA 3-A
- CE Marked

---

© 2016 Eaton. All rights reserved.