



Powering Business Worldwide

pe.eaton.com

30.5 mm, Corrosion Resistant, Assembled Push-Pull Unit

E34GDBC2-1

UPC:782114375716

Dimensions:

- **Height:** 3.2 IN
- **Length:** 2.4 IN
- **Width:** 2.1 IN

Weight: .4 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Corrosion Resistant
- **Actuator:** Standard
- **Actuator Color:** Red
- **Bus Material:** Plastic
- **Contact Configuration:** 1NO-1NC
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position
- **Operating Mode:** Maintained push and pull
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** E34

Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked



- FDA 3-A

© 2016 Eaton. All rights reserved.