



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## 30.5 mm, Corrosion Resistant Push-Pull Operator

E34GDBC2

UPC:782113818030

### Dimensions:

- **Height:** X
- **Length:** X
- **Width:** X

**Notes:** Use NEMA 4X 10250T operators where exposed to ultraviolet light

### Warranties:

- 1 year

### Specifications:

- **Type:** 30.5 mm, Corrosion Resistant
- **Actuator:** Standard
- **Actuator Color:** Red
- **Bus Material:** Plastic
- **Illumination:** Non-illuminated
- **Number Of Positions:** Two-position
- **Operating Mode:** Maintained push and pull
- **Size:** 40 mm
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** E34

### Supporting documents:

- [10250T and E34 Class I Division 2](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Cam selection for pushbutton selectors](#)

### Certifications:

- CSA Certified
- UL Listed

### Product compliance:

- CE Marked
- FDA 3-A



