



Powering Business Worldwide

pe.eaton.com

Eaton's Meter Breaker EUSERC

MBE1428B125BF

UPC:782114849071

Dimensions:

- **Height:** 34.13 IN
- **Length:** 5.38 IN
- **Width:** 14.44 IN

Weight:42 LB

Warranties:

- 10 year

Specifications:

- **Type:** All-in-ones
- **Amperage Rating:** 125A
- **Box Size:** B
- **Bus Material:** Aluminum
- **Enclosure:** NEMA 3R
- **Feed Type:** Underground
- **Ground:** #14-2/0 AWG
- **Interrupt Rating:** 10 kAIC
- **Line:** #6-250 kcmil
- **Main Circuit Breaker:** BR2125
- **Mounting:** Flush mounting
- **Number Of Circuits:** 28
- **Number Of Jaws:** Four-jaws
- **Number Of Sockets:** 1
- **Number Of Spaces:** 14
- **Phase:** Single-phase
- **Security:** Ring
- **Used With:** Type BR breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Technical Data Residential Meter Breakers:](#)



Type CH and BR Residential

Certifications:

- UL Listed

Product compliance:

- EUSERC Approved

© 2016 Eaton. All rights reserved.