

Three-Phase Encapsulated—Type EPT, 60 Hz**480 Delta Volts to 480Y/277 Volts**

| kVA | Full Capacity Taps | | Type | °C Temp. Rise | Frame | Wiring Diagram Number | Weight Lbs (kg) | Weathershield | Catalog Number |
|-----|--------------------|------------|------|---------------|-------|-----------------------|-----------------|----------------|---------------------|
| | FCAN | FCBN | | | | | | | |
| 9 | 2 at +2.5% | 2 at -2.5% | EPT | 115 | FR103 | 72C | 190 (86) | Indoor-Outdoor | Y48D47T09N ① |
| 15 | 2 at +2.5% | 2 at -2.5% | EPT | 115 | FR95 | 72C | 275 (125) | Indoor-Outdoor | Y48D47T15N ① |
| 30 | 2 at +2.5% | 4 at -2.5% | EPT | 115 | FR243 | 84A | 422 (191) | Indoor-Outdoor | Y48M47T30N |
| 45 | 2 at +2.5% | 4 at -2.5% | EPT | 115 | FR244 | 84A | 660 (299) | Indoor-Outdoor | Y48M47T45N |

600 Delta Volts to 208Y/120 Volts

| kVA | Full Capacity Taps | | Type | °C Temp. Rise | Frame | Wiring Diagram Number | Weight Lbs (kg) | Weathershield | Catalog Number |
|-----|--------------------|------------|------|---------------|-------|-----------------------|-----------------|----------------|---------------------|
| | FCAN | FCBN | | | | | | | |
| 9 | — | 2 at -5% | EPT | 115 | FR103 | 70B | 185 (84) | Indoor-Outdoor | Y60G28T09N ① |
| 15 | — | 2 at -5% | EPT | 115 | FR95 | 70B | 275 (125) | Indoor-Outdoor | Y60G28T15N ① |
| 30 | 2 at +2.5% | 4 at -2.5% | EPT | 115 | FR243 | 84B | 422 (191) | Indoor-Outdoor | Y60M28T30N |
| 45 | 2 at +2.5% | 4 at -2.5% | EPT | 115 | FR244 | 84B | 660 (299) | Indoor-Outdoor | Y60M28T45N |

Three-Phase Shielded—Type EPT, 60 Hz**480 Delta Volts to 208Y/120 Volts**

| kVA | Full Capacity Taps | | Type | °C Temp. Rise | Frame | Wiring Diagram Number | Weight Lbs (kg) | Weathershield | Catalog Number |
|-----|--------------------|------------|------|---------------|-------|-----------------------|-----------------|----------------|---------------------|
| | FCAN | FCBN | | | | | | | |
| 3 | 2 at +2.5% | 2 at -2.5% | EPT | 115 | FR201 | 86B | 116 (52) | Indoor-Outdoor | Y48D28E03A ① |
| 6 | 2 at +2.5% | 2 at -2.5% | EPT | 115 | FR200 | 86B | 165 (75) | Indoor-Outdoor | Y48D28E06A ① |
| 9 | 2 at +2.5% | 2 at -2.5% | EPT | 115 | FR103 | 86B | 190 (86) | Indoor-Outdoor | Y48D28E09N ① |
| 15 | 2 at +2.5% | 2 at -2.5% | EPT | 115 | FR95 | 86B | 275 (125) | Indoor-Outdoor | Y48D28E15B ① |

480 Delta Volts to 240 Delta Volts

| kVA | Full Capacity Taps | | Type | °C Temp. Rise | Frame | Wiring Diagram Number | Weight Lbs (kg) | Weathershield | Catalog Number |
|-----|--------------------|------------|------|---------------|-------|-----------------------|-----------------|----------------|---------------------|
| | FCAN | FCBN | | | | | | | |
| 3 | — | 2 at -5% | EPT | 115 | FR201 | 88A | 116 (52) | Indoor-Outdoor | Y48G24E03A ① |
| 6 | — | 2 at -5% | EPT | 115 | FR200 | 88A | 165 (75) | Indoor-Outdoor | Y48G24E06A ① |
| 9 | — | 4 at -2.5% | EPT | 115 | FR103 | 505B | 195 (89) | Indoor-Outdoor | Y48J24E09A ① |
| 15 | — | 4 at -2.5% | EPT | 115 | FR95 | 505B | 275 (125) | Indoor-Outdoor | Y48J24E15A ① |

Notes

① T-T connected secondary.

Contact your local Eaton sales office for CE Mark transformer requirements. For other ratings or catalog numbers not shown, or for special enclosure types (including stainless steel), refer to Eaton. Frame drawings/dimensions information begins on **Page V2-T2-215**.