



SP105/41/MOG

105W 120V Spiral 4100K Mogul Base

Specifications	
Item	SP105/41/MOG
Bar Code	81185
Volts	120
Watts	105
MOL in/mm	11.26/286
MOD in/mm	4.02/102
Avg Life	10000
Base	Mogul Screw (E39)
Special Desc	Not for use with dimmers, electronic timers, photocells, motion/occupancy sensors, or in totally enclosed fixtures. Use in dry locations only. Use in open socket type fixtures only.
Ambient Operating Temp Range	Max ambient temp 104°F. Open socket type fixture.
CT deg K	4100
Photo No	849
Replaces	Std 420W Incandescent
CRI	>80
Approx Initial Lumens	7000
Approvals	UL/CSA, TCLP Compliant
Mercury Content (mg)	4.8
Documentation	http://eiko.com/ContentFiles/Image/ftc_label/SP105_41K_MOG_ftc_label.jpg target="_blank">FTC Label