



|                      |                                       |
|----------------------|---------------------------------------|
| <b>Description</b>   | 1000W BT-56 Mogul Base Universal Burn |
| <b>Ordering Code</b> | 49199                                 |
| <b>UNSPSC Code</b>   | 39101614                              |

## Specifications

|                              |                   |
|------------------------------|-------------------|
| <b>Watts</b>                 | 1000              |
| <b>Base Type</b>             | Mogul Screw (E39) |
| <b>Bulb Type</b>             | BT-56             |
| <b>MOL in/mm</b>             | 15.5/393.7        |
| <b>MOD in/mm</b>             | 7.09/180          |
| <b>LCL in/mm</b>             | 9.50/241.0        |
| <b>Mercury Content (mg)</b>  | 82.5              |
| <b>HG Form</b>               | liquid            |
| <b>Approx Initial Lumens</b> | 110000            |
| <b>Approx Mean Lumens</b>    | 71000             |
| <b>CT deg K</b>              | 4000              |
| <b>CRI</b>                   | 70                |
| <b>Rated Life</b>            | 12,000            |
| <b>Common Code</b>           | MVR1000/U         |
| <b>ANSI Ballast</b>          | M47               |
| <b>Fixt Rqmt</b>             | Enclosed          |
| <b>Burning Position</b>      | Universal         |
| <b>Special Desc</b>          | Probe Start       |
| <b>Coating</b>               | Clear             |

watch > like > follow



selection. solutions. simplicity. [eiko.com](http://eiko.com)

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335