



Description	400W Open Rated Pulse ED37 Base Up EX39 Mogul Base
Ordering Code	06276
UNSPSC Code	39101614

Specifications

Watts	400
Base Type	Mogul Screw with Long Prong (EX39)
Bulb Type	ED-37
MOL in/mm	11.73/296
LCL in/mm	7.17/182
Mercury Content (mg)	55
HG Form	liquid
Approx Initial Lumens	41000
Approx Mean Lumens	28000
CT deg K	4000
CRI	65
Rated Life	20,000
Common Code	MP400/U/ED37/PS
ANSI Ballast	M155/M128/M135/O
Fixt Rqmt	Open
Burning Position	BU
Special Desc	Pulse Start & UV Shielded
Coating	Clear

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335