

LINE VOLTAGE RECESSED

4" HOUSINGS

Recessed Lighting

All 4" Line Voltage Housings are:

- UL damp location listed
- UL feed through listed
- Can be retrofitted to use 120V MR16 lamps with PSA28 adapter.



4" Miniature Housing

EL99

EL99A (airtight) NEW!

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max



4" Miniature Airtight IC Housing

EL99ICA

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max



4" Miniature Remodel Housing

EL99R

EL99RA (airtight) NEW!

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max

4" HOUSINGS for 120V MR16

The following housings *only* work with 4" Low Voltage trims on pages 64-69.



4" Miniature Housing for 120V MR16

EL1299

- Height: 5 1/2"
- Opening: 4 1/4"
- Lamp: 50W max
- Lamp is included



4" Miniature Remodel Housing for 120V MR16

EL1299R

- Height: 5 7/8"
- Opening: 4 1/4"
- Lamp: 50W max
- Lamp is included

LINE VOLTAGE RECESSED

BAFFLE TRIMS 4"

Recessed Lighting



Airtight Baffle Cone Trim

EL902W All White

Lamp: 75W PAR30

O.D.: 5 1/16"



Phenolic Baffle with Metal Ring

EL993W All White

EL993N All Nickel

EL993BZW Bronze Bfl. White Ring

EL993BZ All Bronze

EL993CP All Copper

EL993NW Nickel Bfl. White Ring

EL993WBZ White Bfl. Bronze Ring

EL993WG White Bfl. Gold Ring

EL993WN White Bfl. Nickel Ring

Lamp: 40W R16, 50W PAR20, R20

O.D.: 4 3/4"



Diecast Round Stepped Trim

EL941B Black Bfl. White Ring

EL941W All White

Lamp: 50W PAR20, R20

O.D.: 4 3/4"



Pinhole Trim with Baffle

EL990W Black Bfl. White Ring

EL990BZ All Bronze **NEW!**

EL990CP All Copper **NEW!**

EL990N All Nickel

Lamp: 55W R16, 50W PAR20, R20

I.D.: 2", O.D.: 4 7/8"



Metal Baffle with Metal Ring

EL993MB Black Bfl. White Ring

EL993MW All White

Lamp: 50W PAR20, R20

O.D.: 4 3/4"



Black Phenolic Baffle with Metal Ring

EL993B Black Bfl. White Ring

EL993BCP Black Bfl. Copper Ring

EL993BB All Black

EL993BC Black Bfl. Clear Ring

EL993BG Black Bfl. Gold Ring

EL993BN Black Bfl. Nickel Ring

Lamp: 40W R16, 50W PAR20, R20

O.D.: 4 3/4"



Phenolic Baffle with Metal Ring and Lamp Holder Bracket

EL993KBN Black Bfl. Nickel Ring

EL993KB All Black

EL993KCPW Copper Bfl. White Ring

EL993KN All Nickel

EL993KW All White

Lamp: 40W A19, 40W R16,

50W PAR20, R20

O.D.: 4 3/4"