

LINE VOLTAGE RECESSED

6" HOUSINGS

Recessed Lighting

S Trims with this symbol are compatible with shallow housings.



6" Shallow Housing

R9H

- Height: 5 1/2"
- Opening: 6 1/2"
- Lamp: 75W max



6" Airtight IC Shallow Housing

R9ICA

- Height: 5 1/2"
- Opening: 6 1/2"
- Lamp: 75W max



6" Airtight IC Shallow Remodel Housing

RR9ICA

- Height: 5 1/2"
- Opening: 6 1/2"
- Lamp: 75W max



6" Shallow Remodel Housing

RR9H

- Height: 5 1/2"
- Opening: 6 1/2"
- Lamp: 75W max

LINE VOLTAGE RECESSED

BAFFLE TRIMS 6"

Recessed Lighting



Wide Flanged Baffle

- EL304B** Black
- EL304BG** Black Bfl. Gold Ring
- EL304W** All White
- EL304WG** White Bfl. Gold Ring
- Lamp: 75W PAR30, R30
- O.D.: 8"



Airtight Clear Reflector with Baffle

- ELA101WA** Nickel Bfl. White Ring
- Lamp: 75W PAR30, R30, 100W A19
- O.D.: 7 1/4"



Clear Reflector with Baffle

- ELA101B** Black Bfl. White Ring
- ELA101N** Nickel Bfl. Nickel Ring
- ELA101CP** Copper Bfl. Copper Ring
- ELA101BZ** Bronze Bfl. Bronze Ring
- ELA101NB** Nickel Bfl. Black Ring
- ELA101NW** Nickel Bfl. White Ring
- ELA101W** White Bfl. White Ring
- Lamp: 75W PAR30, R30, 100W A19
- O.D.: 7 1/4"



Metal Baffle

- ELM30B** Black Bfl. White Ring
- ELM30W** All White
- ELM30BG** Black Bfl. Gold Ring
- ELM30BB** All Black
- ELM30BZ** All Bronze **NEW!**
- ELM30BBZ** Black Bfl. Bronze Ring
- ELM30BCP** Black Bfl. Copper Ring
- ELM30BZB** Bronze Bfl. Black Ring
- ELM30BZW** Bronze Bfl. White Ring
- ELM30CP** All Copper **NEW!**
- ELM30CPB** Copper Bfl. Black Ring
- ELM30CPW** Copper Bfl. White Ring
- ELM30N** All Nickel
- ELM30NB** Nickel Bfl. Black Ring
- ELM30NW** Nickel Bfl. White Ring
- ELM30W** All White
- ELM30WBZ** White Bfl. Bronze Ring
- ELM30WCP** White Bfl. Copper Ring
- ELM30WG** White Bfl. Gold Ring
- Lamp: 75W PAR30, R30
- O.D.: 7 1/4"



Metal Baffle with Oversized Ring

- ELM30BOV** Black Bfl. White Ring
- ELM30WOV** All White
- Lamp: 75W PAR30, R30
- O.D.: 8"