

LINE VOLTAGE RECESSED

6" ADJUSTABLE TRIMS

LINE VOLTAGE RECESSED

SLOPED HOUSINGS 6"

Recessed Lighting



Regressed Eyeball with Baffle

ELM48W All White
ELM48N All Nickel
ELM48BZ All Bronze **NEW!**
ELM48CP All Copper **NEW!**
Lamp: 75W R30
O.D.: 7 1/4"



Regressed Eyeball with Baffle

ELM48B Black Bfl.
White Eyeball White Ring
ELM48BB Black Bfl.
Black Eyeball White Ring
ELM48BG Black Bfl.
Gold Eyeball White Ring
ELM48BGG Black Bfl.
Gold Eyeball Gold Ring
ELM48NW Nickel Bfl.
White Eyeball Nickel Ring
ELM48WG White Bfl.
Gold Eyeball White Ring
ELM48WGG White Bfl.
Gold Eyeball Gold Ring
Lamp: 75W R30
O.D.: 7 1/4"

6" WALL WASH TRIMS



Wall Wash
EL25W All White
Lamp: 60W A19
O.D.: 8"



Wall Wash with Baffle and Reflector
ELA105B Black Bfl. White Trim
ELA105W All White
Lamp: 60W A19, 75W R30
O.D.: 7 1/4"



Wall Wash with Metal Baffle
ELM45B Black Bfl. White Trim
ELM45W All White
Lamp: 60W A19, 75W R30
O.D.: 7 1/4"

For all housings on this page:

- Elliptical aperture and trim ring match ceiling slope
- UL damp location listed
- UL feed through listed



6" Sloped Housing

- EL900HT
- Height: 7 1/2"
 - Opening: 6 1/2" x 6 3/4"
 - Lamp: 150W max



6" Sloped Remodel Housing

- EL900RT
- Height: 7 1/2"
 - Opening: 6 1/2" x 6 3/4"
 - Lamp: 150W max



6" Airtight IC Sloped Housing

- EL918ICA
- Height: 7 1/2"
 - Opening: 6 1/2" x 6 3/4"
 - Lamp: 75W max



6" Airtight IC Sloped Remodel Housing

- EL918RICA **NEW!**
- Height: 7 1/2"
 - Opening: 6 1/2" x 6 3/4"
 - Lamp: 75W max



6" Airtight IC Sloped Housing

- EL936ICA
- Height: 7 1/2"
 - Opening: 6 1/2" x 6 3/4"
 - Lamp: 90W max

Recessed Lighting