



The Corrlok® System

TYPE - CLL



Contact your local Sales Representative
[Click Here for Printable Version](#)

				Nominal	Dimensions			Std	Footage	List Price
Type	US Trade Size	MM	Nw	Inside	Outside	Min. Inside Bend Radius Static	Wt. (LBS.)/100Ft	Length	Part #	Price Per 100 FT
CLL-10	3/8"	16	12	.452"(11.5mm)	.622"(15.8mm)	0.7"	3.4	100	790816	\$63.00
CLL-11	1/2"	20	17	.633"(16.1mm)	.826"(21.0mm)	0.8"	4.4	100	791816	\$72.00
CLL-12	3/4"	25	23	.865"(22.0mm)	1.122"(28.5mm)	1.2"	6.7	100	792816	\$109.00
CLL-13	1"	32	29	1.087"(27.6mm)	1.358"(34.5mm)	1.4"	9.1	50	793816	\$132.00
CLL-14	1-1/4"	40	36	1.420"(36.0mm)	1.673"(42.5mm)	2.4"	11.0	50	794816	\$320.00
CLL-15	1-1/2"	50	48	1.850"(47.00mm)	2.145"(54.5mm)	2.8"	16.0	50	795816	\$394.00
CLL-17	2-1/2"	70	70	2.645"(67.0mm)	3.150"(80.0mm)	6.3"	32.0	30	79686	\$1,064.00
CLL-350	3-1/2"	95	95	3.600"(91.5mm)	4.170"(106mm)	8.3"	52.0	30	79886	\$1,555.00

*Reels available. Consult factory.

See [Corrlok Information Page](#)

TYPE - CLL

This lightweight version provides many of the same qualities of Type CL but with improved flexibility.

UL Recognized Component File #E174249 600 Volt, 105 Degrees ©, Vertical Flame, Liquidtight, UV and Impact Tested.

Fittings:

To be used with the Corrlok® connectors of the Corrlok® System

Fitting Pull-Out:

40 lbs. (1/2" and larger)

Material:

Halogen Free Nylon 6

STANDARD COLORS:

Black. [Other colors available upon request](#)