

# B26IC

Applications: **P** **IC**

6" SHALLOW IC HOUSING

## 6" SHALLOW IC HOUSING

### Lamp Wattage:

(1) Maximum 75W R/PAR30, 60W A19, 65W BR30



6"		
B26IC • B607CL 75W PAR30 NFL LAMP		
5'	136	2.7'
8'	53	4.3'
10'	34	5.4'
12'	24	6.4'
Distance to Plane	Initial Nadir Footcandles	Beam Spread

BEAM DIA. MEASURED AT 50% OF NADIR F.C.

### DESCRIPTION:

For new construction. Thermally protected, IC rated specification grade recessed housing. Accommodates up to 75W PAR30, R30 lamps, 60W A19 lamps and 65W BR30 lamps. Furnished with preinstalled adjustable bar hangers. Junction box is provided with four 1/2" KOs, one 3/4" KO and four Romex knockouts with strain relief.

### SPECIFICATION:

**A. HOUSING** - Die-formed all aluminum construction for maximum heat dissipation and rust protection. Adjusts vertically in plaster frame to accommodate 1/2" to 1-3/8" ceiling.

**B. SOCKET** - Medium base screw shell porcelain socket preinstalled on adjustable mounting bracket is designed to allow usage of different lamp types, as well as proper and consistent lamp positioning.

**C. BAR HANGERS** - Preinstalled bar hangers allow housing to be positioned and locked at any point within a 24" joist span. They can be positioned on either the long or short axis of the housing and can be shortened for 12" joists. They contain a double-headed real nail for secure attachment into the joist. Bar hanger nails are installed on a 20° downward angle for better contact, and the 90° pivoting mounting plate makes installation fast and accurate. Bar hangers can fit onto T-Bar spline with additional slots and holes for special mounting methods if necessary.

**D. JUNCTION BOX** - UL and ETL listed for through-branch circuit wiring and has four 1/2" KOs, one 3/4" KO and four Romex knockouts with true pry-out slots and strain clamps.

**E. THERMAL PROTECTION** - Standard thermal protection device guards against improper installation, overlampping and misuse of insulation material.

**UL and C-UL listed  
ETL and C-ETL listed**

For Damp location  
For Feed-through wiring  
For Direct contact with insulation

### FEATURES:



- Thermally Protected Shallow IC Housing.
- Adjustable Socket bracket.
- Wire through junction box.
- Preinstalled adjustable Bar Hanger.
- Dependable, favorable design and effortless installation.
- 5 1/2" height allows use in 2"x 6" joist construction.
- Special screw on the frame locks bar hangers in place which prevents the housing from any movement once installed.
- Preinstalled socket cap provides electrical contact protection against dust, paint and over spray.

### OPTION:

- AIR-SHUT-**
  - Gasket to prevent air flow from heated or air conditioned spaces.
  - Meets all national air flow requirements.

ITEM SELECTOR: (Please check the boxes below for the option desired)

TYPE	OPTION(S)	
<input type="checkbox"/> B26IC	<input type="checkbox"/> AIR SHUT	<input type="checkbox"/> WITH QUICK CONNECTS
	<input type="checkbox"/> AT	<input type="checkbox"/> W



6"

INCANDESCENT