



APPLICATION:

Suitable for retail displays, gondolas, cove and undercabinet applications.

PRODUCT FEATURES:

- Built-in electronic ballast
- Energy-efficient
- Uses standard T5 lamps
- Plug-in modular system permits easy connection for continuous lighting
- Extremely long lamp life, manufacturer rated for 10,000 hrs
- Available in four different lengths: 1' (12-3/8"), 2' (22-5/8"), 3' (34-1/2"), 4' (46-1/2") and 5' (58-1/16") width: 15/16", height: 1-5/8"
- Acrylic cover is standard
- Contemporary white housing

- More light
- Less heat
- Easier installation
- More flexibility

LISTING

UL/C-UL listed to US and Canadian standard

WARRANTY

Guaranteed for one year against mechanical defects

Ordering Information > Example: EUM-T5-8W-120

SERIES	FIXTURE SIZE/LAMP TYPE (Included)	VOLTAGE	OPTIONS
EUM-T5	<p>12" FIXTURE</p> <p>8W - (1 lamp/8W/T5)-(12-3/8"L X 1-5/8"H X 15/16"W)</p> <hr/> <p>22" FIXTURE</p> <p>14W - (1 lamp/14W/T5)-(22-5/8"L X 1-5/8"H X 15/16"W)</p> <p>24W - (1 lamp/24W/T5HO)-(22-5/8"L X 1-5/8"H X 15/16"W)</p> <hr/> <p>35" FIXTURE</p> <p>21W - (1 lamp/21W/T5)-(34-1/2"L X 1-5/8"H X 15/16"W)</p> <p>39W - (1 lamp/39W/T5HO)-(34-1/2"L X 1-5/8"H X 15/16"W)</p> <hr/> <p>46" FIXTURE</p> <p>28W - (1 lamp/28W/T5)-(46-1/8"L X 1-5/8"H X 15/16"W)</p> <p>54W - (1 lamp/54W/T5HO)-(46-1/8"L X 1-5/8"H X 15/16"W)</p> <hr/> <p>58" FIXTURE</p> <p>35W - (1 lamp/35W/T5)-(58-1/16"L X 1-5/8"H X 15/16"W)</p>	120	<p>EUM-1 - Link connector</p> <p>EUM-2 - 6" Flexible connector</p> <p>EUM-4 - 6' Power cord</p> <p>EUM-7 - Stainless steel mounting clip</p> <p>EUM-8 - Polycarbonate mounting clip</p> <p>EUM-9 - Hardware box</p>

Accessories



EUM-1
LINK CONNECTOR



EUM-2
6" FLEXIBLE WIRE CONNECTOR



EUM-4
6' POWER CORD



EUM-7
STAINLESS STEEL MOUNTING CLIP



EUM-8
POLYCARBONATE MOUNTING CLIP



EUM-9
HARDWARE BOX