

North American Region

Download Instructions and Warranty Information

English | Français | Español



15 Minute Charger



VERSATILE

- Charges 1 to 4 AA or AAA NiMH batteries

COMPACT

- Charger and AC adapter small, sleek design

MOBILE

- Includes car adapter

FAST

- Batteries ready for use in 15 minutes (2200 mAh AA)

SMART

- Automatically detects battery size and has LED indicators

Product Detail:

Designation: 15 Minute Charger

Color: Charcoal Grey

Charge Capability: "AA" (1) to (4) "AAA" (1) to (4)

Charge Duration: Primary = 20 minutes Secondary = 24 hours

Charging Current: "AA" Primary = 7500 mA

"AA" Secondary = 100 mA

"AAA" Primary = 2850 mA

"AAA" Secondary = 35 mA

Charging Times: (estimated)	Battery (NiMH)	Capacity (mAh)	Estimated (time)*
	AA	2500-2650	19 min
	AA	2450	18 min
	AA	2200	16 min
	AA	2000	14.5 min
	AAA	1000	19 min
	AAA	900	17 min
	AAA	850	15 min

Shutoff Mechanism: Delta V Detection
Temperature Detection
Timer Control

Charger Input: DC 11-16V, 5A

AC Adapter Input: 120vac~60Hz, 85W

Weight (charger): 180 grams (6.3 oz.)

Dimensions (mm): 40 x 131 x 78 (H x L x W)

Rev Polarity Protection: Yes

Primary Battery Detection: Yes

* Per American National Standards Institute (ANSI) standard.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc.

Contents herein do not constitute a warranty.

Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer NiMH batteries.

Note: Batteries may become hot to the touch while charging.