

Cable/Conduit

Multi-Function Clip

From Drop Wire, Plain Threaded Rod, or Flange

Features

- Attaches to #12 wire thru 3/8" rod
- Fits 1/8" to 3/8" flanges
- Provides attachment of conduit and boxes
- Supports #10-24 and 1/4-20 threaded bridle rings
- Supports 4" or 4-11/16" electrical box



Fig. #1



Part Number	Fig. #	Description	Wire/Rod Size (in)
4Z34	1	Multi-function clip	#12 wire - 1/4"
4Z4S	2	Multi-function clip with 1/4-20 stud and hex nut	#12 wire - 1/4"
4Z34812M	3	Multi-plus 1/2" or 3/4" conduit	#12 wire - 1/4"
4Z3416M	3	Multi-plus 1" conduit	#12 wire - 1/4"
4Z348P*	4	Multi-plus 1/2" EMT conduit	#12 wire - 1/4"
4Z3412P*	4	Multi-plus 3/4" EMT conduit	#12 wire - 1/4"
4Z3416P*	4	Multi-plus 1" EMT conduit	#12 wire - 1/4"
6Z34	1	Multi-function clip	3/8" rod
6Z4S	2	Multi-function clip	3/8" rod
6Z34812M	3	Multi-plus 1/2" or 3/4" conduit	3/8" rod
6Z3416M	3	Multi-plus 1" conduit	3/8" rod
6Z348P*	4	Multi-plus 1/2" EMT conduit	3/8" rod
6Z3412P*	4	Multi-plus 3/4" EMT conduit	3/8" rod
6Z3416P*	4	Multi-plus 1" EMT conduit	3/8" rod

*When using rigid conduit on P-Series, use next size larger clip (1/2" Rigid use 12P)

Standard Packaging Quantity: 100

Notes: NEC 300.11 requires dedicated drop wire/rod and EC311

When using rigid conduit on P series, use next size larger clip (1/2" Rigid use 12P)

4Z series designates 1/8"-3/8" Flange Size

6Z series designates 3/8"-7/16" Flange Size



Fig. #2



Fig. #3



Fig. #4