

Cable/Conduit



Fig. #2

Part Number	Fig. #	Description	Standard Packaging Quantity
6M24SM†	2	3/8" MC/AC cable to 1/8" to 1/4" flanges (Sidemount)	100
6M58SM†	2	3/8" MC/AC cable to 5/16" to 1/2" flanges (Sidemount)	100
6M912SM†	2	3/8" MC/AC cable to 9/16" to 3/4" flanges (Sidemount)	100
812M24SM†	2	1/2" to 3/4" conduit to 1/8" to 1/4" flanges (Sidemount)	100
812M58SM†	2	1/2" to 3/4" conduit to 5/16" to 1/2" flanges (Sidemount)	100
812M912SM†	2	1/2" to 3/4" conduit to 9/16" to 3/4" flanges (Sidemount)	100
16M24SM†	2	1" conduit to 1/8" to 1/4" flanges (Sidemount)	100
16M58SM†	2	1" conduit to 5/16" to 1/2" flanges (Sidemount)	100
16M912SM†	2	1" conduit to 9/16" to 3/4" flanges (Sidemount)	100
20M24SM†	2	1 1/4" conduit to 1/8" to 1/4" flanges (Sidemount)	100
20M58SM†	2	1 1/4" conduit to 5/16" to 1/2" flanges (Sidemount)	100
20M912SM†	2	1 1/4" conduit to 9/16" to 3/4" flanges (Sidemount)	50
24M24SM†	2	1 1/2" conduit to 1/8" to 1/4" flanges (Sidemount)	50
24M58SM†	2	1 1/2" conduit to 5/16" to 1/2" flanges (Sidemount)	50
24M912SM†	2	1 1/2" conduit to 9/16" to 3/4" flanges (Sidemount)	50
32M24SM†	2	2" conduit to 1/8" to 1/4" flanges (Sidemount)	50
32M58SM†	2	2" conduit to 5/16" to 1/2" flanges (Sidemount)	50
32M912SM†	2	2" conduit to 9/16" to 3/4" flanges (Sidemount)	50

*Load Limit: 75 lbs (static)

†Load Limit: 25 lbs (static)