

CADDY® CABLECAT

Wide Base Cable Support Clips -
2" Diameter Loop



Part Number	Fig. #	Description	Standard Packaging Quantity
CAT324Z34	1	2" J-Hook assembled to 4Z34 - #12 thru 1/4" wire, plain or threaded rod and 1/8" thru 3/8" flange	40
CAT326Z34	1	2" J-Hook assembled to 6Z34 - 3/8" plain or threaded rod and 3/8" thru 7/16" flange	40
CAT32AB	2	2" J-Hook assembled to angle bracket - 1/4" mounting hole	40
CAT32AFAB3	3	2" J-Hook assembled to Angle Bracket Assembly - 3/16" mounting hole	40
CAT32AFAB4	3	2" J-Hook assembled to Angle Bracket Assembly - 1/4" mounting hole	40
CAT32AFAB6	3	2" J-Hook assembled to Angle Bracket Assembly - 3/8" mounting hole	40
CAT32VF14	4	2" J-Hook assembled to C purlin bracket - 1/16" thru 1/4" vertical flange	40
CAT32912SM	5	2" J-Hook assembled to hammer-on 1/2" thru 3/4" flange - side mount	40
CAT32912	6	2" J-Hook assembled to hammer-on 1/2" thru 3/4" flange - bottom mount rotates 360°	20
CAT3224SM	5	2" J-Hook assembled to hammer-on 1/8" thru 1/4" flange - side mount	40
CAT3224	6	2" J-Hook assembled to hammer-on 1/8" thru 1/4" flange - bottom mount rotates 360°	20
CAT3258SM	5	2" J-Hook assembled to hammer-on 5/16" thru 1/2" flange - side mount	40
CAT3258	6	2" J-Hook assembled to hammer-on 5/16" thru 1/2" flange - bottom mount rotates 360°	20
CAT32BC	7	2" J-Hook assembled to screw-on bracket - 1/8" thru 1/2" flange	40
CAT32BC200	8	2" J-Hook assembled to screw-on bracket - 1/8" thru 5/8" flange	20
CAT32BC200B	9	2" J-Hook assembled to screw-on bracket - 1/8" thru 5/8" flange - rotates 360°	20
CAT32BCB	7	2" J-Hook assembled to screw-on bracket 1/8" thru 1/2" flange - rotates 360°	20
CAT32CD1B	10	2" J-Hook assembled to under floor support to pedestal	20
CAT32AF14	11	2" J-Hook assembled to Z purlin bracket - 1/16" thru 1/4" Z purlin	40
CAT32ESC	12	Snap-in 2" Diameter J-Hook	40

