



Dependable Power for Any Application

Product Datasheet

95-132 X 166-228 X 192-264 X 384-528 Primary Volts -
120/208/240 Secondary Volts - 1Ø
Power Conditioning - Hardwired Models

Catalog #: T169435



PRODUCT FEATURES

- Input range of +10/-20%
- Effective noise rejection
- UL Listed and CSA Certified
- Encapsulated transformer
- Covered under Acme's 10 year limited warranty

BENEFITS

- Suppressing transient spikes and surges
- Rapid response to line and load changes
- Inherent overload and short circuit protection

UL STANDARD

UL 1012

CSA STANDARD

C22.2 No. 66

WARRANTY

Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf

GENERAL PRODUCT INFORMATION

kVA:	2.00
Primary Voltage:	95-132 X 166-228 X 192-264 X 384-528
Secondary Voltage:	120/208/240
Frequency:	60 Hz
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

PRODUCT MEASUREMENTS

Height (In./cm):	19 (48.3)
Width (In./cm):	10.5 (26.7)
Depth (In./cm):	10.2 (25.9)

CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Floor/Wall
Wiring Diagram:	16

PACKAGING

Ship Weight (Lbs/Kg):	142 (64.4)
-----------------------	------------

COMPLIANCES

UL Standard:	UL 1012
UL Listed:	File E86492
CSA Standard:	C22.2 No. 66
CSA Listed:	LR7357-33
Warranty:	Acme Electric Warranty Card
www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf	

