



Dependable Power for Any Application

# Product Datasheet

Copper Windings - 240 X 480 Primary Volts - 120/240  
Secondary Volts - Four Windings - 1Ø  
Dry Type Distribution Transformer - Single Phase

Catalog #: TC535173S



## PRODUCT FEATURES

- UL listed, CSA certified
- Fully encapsulated core and coil
- Meet CSA C802.2 Efficiency
- UL Type 3R epoxy encapsulated
- Wall Mounted
- Ground Studs for use with non-metallic conduit
- Copper lead wire terminations
- Covered under Acme's 10 year limited warranty

---

## BENEFITS

- Quiet operation with sound levels below NEMA standards
- Electrostatic shield for enhanced protection

---

## UL STANDARD

UL 506

---

## CSA STANDARD

C22.2 No. 47

---

## WARRANTY

Acme Electric Warranty Card  
[www.hubbell-acmeElectric.com/Images/news/Acme\\_Warranty.pdf](http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf)

## GENERAL PRODUCT INFORMATION

kVA:	15.00
Primary Voltage:	240 X 480
Secondary Voltage:	120/240
Frequency:	60 Hz
ANFC Taps:	2
BNFC Taps:	4
Taps % Steps:	2.5%
Max Temperature Rise:	115°C
UL Insulation Class:	180°C

## PRODUCT MEASUREMENTS

Height (In./cm):	16.94 (43.0)
Width (In./cm):	14.12 (35.9)
Depth (In./cm):	11.59 (29.4)

## CONFIGURATION

Construction Type:	Encapsulated
Mounting Type:	Wall
Knockouts (In./Cm):	1.00-1.50 (2.5-3.8)
Wiring Diagram:	4

## PACKAGING

Ship Weight (Lbs/Kg):	160 (72.6)
-----------------------	------------

## COMPLIANCES

UL Standard:	UL 506
UL Listed:	File E79947
CSA Standard:	C22.2 No. 47
CSA Listed:	LR7357-32
Warranty:	Acme Electric Warranty Card
	<a href="http://www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf">www.hubbell-acmeElectric.com/Images/news/Acme_Warranty.pdf</a>