

EGBA Series – 1/4" Thick

Standard Configurations in Stock



Busbars

- 1/4" thick copper
- ASTM B187-C11000
- Electro-tin plating available (add "T" to part number)

Brackets

- Type 304 stainless steel
- 1/8" thick

Insulators (Stand Off)

- Manufactured from a halogen-free, fiberglass-reinforced thermalset polyester molded compound (BMC)
- Meet the requirements of UL® 94 V-0 for self-extinguishing materials
- Indoor rating: 600 volts

Fasteners

- 3/8" Type 304 stainless steel

- All bars shown include insulators, stainless steel brackets, stainless steel mounting bolts, and are UL Listed.
- All illustrations show bars of 12" length. Bars of longer lengths will have additional holes according to the pattern shown.
- Contact ERICO for additional ground bar configurations.

