

Model No.	Part No.	Part Description	List Price 7/1/10	Per	UPC # 782856-	Iten Wt. (lbs.) Per 100	Box/Bundle Qty	Product Class for Pricing
150M (assembled)	150M1200S4	#150 U-Bolt with 4 Nuts 12"	\$34,453.23	HU	51473	773.0	BULK	MT
	150M1400EG	#150 U-Bolt with 4 Nuts 14" EG †	\$7,277.34	HU	36285	828.0	BULK	MT
	150M1400PL	#150 U-Bolt with 4 Nuts 14" †	\$4,913.13	HU	36286	828.0	BULK	MT
	150M1600EG	#150 U-Bolt with 4 Nuts 16" EG	\$8,638.91	HU	36287	915.0	BULK	MT
	150M1600PL	#150 U-Bolt with 4 Nuts 16" †	\$5,694.17	HU	36288	915.0	BULK	MT
	150M1800EG	#150 U-Bolt with 4 Nuts 18" EG †	\$12,396.32	HU	36289	1348.0	BULK	MT
	150M1800PL	#150 U-Bolt with 4 Nuts 18" †	\$8,485.87	HU	36290	1348.0	BULK	MT
	150M2000EG	#150 U-Bolt with 4 Nuts 20" EG †	\$13,509.82	HU	36291	1457.0	BULK	MT
	150M2000PL	#150 U-Bolt with 4 Nuts 20" †	\$8,575.59	HU	36292	1457.0	BULK	MT
	150M2400EG	#150 U-Bolt with 4 Nuts 24" EG †	\$15,288.26	HU	36293	1687.0	BULK	MT
	150M2400PL	#150 U-Bolt with 4 Nuts 24" †	\$9,884.37	HU	36294	1687.0	BULK	MT
150M3000PL	#150 U-Bolt with 4 Nuts 30" †	\$20,876.90	HU	36296	1910.0	BULK	MT	
200	2000037EG	#200 C-Clamp 3/8" with Lock Nut EG	\$400.92	HU	33963	42.0	100	NE
	2000037PL	#200 C-Clamp 3/8" with Lock Nut	\$342.05	HU	36300	42.0	100	NE
200RS	200RS375	Beam Clamp/Rod Hanger/Strut to Flange- 3/8-16 Thread	\$1,146.24	HU	34245	7.0	10	NE
	200RS500	Beam Clamp/Rod Hanger/Strut to Flange- 1/2-13 Thread	\$1,146.24	HU	34247	7.0	10	NE
255	2550037EG	#255 Malleable C-Clamp 3/8" EG	\$500.06	HU	33965	26.0	100	NE
	2550037PL	#255 Malleable C-Clamp 3/8" EG	\$310.05	HU	35403	26.0	100	NE
	2550050EG	#255 Malleable C-Clamp 1/2" EG †	\$604.98	HU	33966	28.0	100	NE
	2550050PL	#255 Malleable C-Clamp 1/2" †	\$360.18	HU	36313	28.0	100	NE
	2550062EG	#255 Malleable C-Clamp 5/8" EG	\$850.60	HU	33967	46.0	50	NE
	2550062PL	#255 Malleable C-Clamp 5/8" †	\$544.65	HU	36314	46.0	50	NE
255C	255C3706EG	#255-C Retainer Strap 3/8" x 6" EG †	\$852.06	HU	33968	23.0	BULK	NE
	255C3708EG	#255-C Retainer Strap 3/8" x 8" EG †	\$1,070.06	HU	33969	30.0	BULK	NE
	255C3710EG	#255-C Retainer Strap 3/8" x 10" EG †	\$1,070.06	HU	33970	36.0	BULK	NE
	255C3714EG	#255-C Retainer Strap 3/8" x 14" EG †	\$1,880.17	HU	33971	50.0	BULK	NE
	255C5006EG	#255-C Retainer Strap 1/2" x 6" EG †	\$875.40	HU	33972	23.0	BULK	NE
	255C5008EG	#255-C Retainer Strap 1/2" x 8" EG †	\$1,101.56	HU	33973	30.0	BULK	NE
255L	255L0037EG	#255-L Malleable C-Clamp with Lock Nut 3/8" EG	\$650.44	HU	35267	26.0	100	NE
	255L0037PL	#255-L Malleable C-Clamp with Lock Nut 3/8"	\$400.96	HU	35596	26.0	100	NE
	255L0050EG	#255-L Malleable C-Clamp with Lock Nut 1/2" EG	\$801.98	HU	36319	29.0	100	NE
	255L0050PL	#255-L Malleable C-Clamp with Lock Nut 1/2" †	\$498.90	HU	36320	29.0	100	NE
	255L0062EG	#255-L Malleable C-Clamp with Lock Nut 5/8" EG	\$1,265.87	HU	36321	47.0	50	NE
	255L0062PL	#255-L Malleable C-Clamp with Lock Nut 5/8" †	\$762.33	HU	36322	47.0	50	NE
280	2800037EG	#280 Reversible Beam Clamp 3/8" EG	\$305.28	HU	58014	34.1	100	NE
	2800037PL	#280 Reversible Beam Clamp 3/8" PL	\$257.15	HU	58015	34.1	100	NE
	2800050EG	#280 Reversible Beam Clamp 1/2" EG	\$544.00	HU	58016	52.4	50	NE
	2800050PL	#280 Reversible Beam Clamp 1/2" PL	\$385.43	HU	58017	52.4	50	NE
300	3000037EG	#300 Reversible Beam Clamp 3/8" EG	\$332.63	HU	33976	33.0	100	NE
	300D0037EG	#300 Reversible Beam Clamp 3/8" EG	\$354.13	HU	58837	33.0	100	NE
	3000037PL	#300 Reversible Beam Clamp 3/8"	\$263.41	HU	34900	33.0	100	NE
	300D0037PL	#300 Reversible Beam Clamp 3/8"	\$296.02	HU	58839	33.0	100	NE
	3000050EG	#300 Reversible Beam Clamp 1/2" EG	\$740.87	HU	33977	64.0	50	NE
	300D0050EG	#300 Reversible Beam Clamp 1/2" EG (Replaces 3000050EG)	\$740.87	HU	58840	64.0	50	NE
	3000050PL	#300 Reversible Beam Clamp 1/2"	\$439.51	HU	34899	64.0	50	NE
	300D0050PL	#300 Reversible Beam Clamp 1/2" (Replaces 3000050PL)	\$439.51	HU	58842	64.0	50	NE
	300D0050HD	#300 Reversible Beam Clamp 1/2" HD	\$1,285.49	HU	58841	64.0	1	NE
	3000062EG	#300 Reversible Beam Clamp 5/8" EG	\$902.51	HU	33978	64.0	50	NE
	300D0062EG	#300 Reversible Beam Clamp 5/8" EG (Replaces 3000062EG)	\$902.51	HU	58843	64.0	50	NE
	3000062PL	#300 Reversible Beam Clamp 5/8"	\$519.49	HU	35093	64.0	50	NE
	300D0062PL	#300 Reversible Beam Clamp 5/8" (Replaces 3000062PL)	\$519.49	HU	58845	64.0	50	NE
	3000075EG	#300 Reversible Beam Clamp 3/4" EG	\$1,203.34	HU	33979	78.0	50	NE
	300D0075EG	#300 Reversible Beam Clamp 3/4" EG (Replaces 3000075EG)	\$1,203.34	HU	58846	78.0	50	NE
	3000075PL	#300 Reversible Beam Clamp 3/4"	\$902.51	HU	36323	78.0	50	NE
	300D0075PL	#300 Reversible Beam Clamp 3/4" (Replaces 3000075PL)	\$902.51	HU	58848	78.0	50	NE
	3000087EG	#300 Reversible Beam Clamp 7/8" EG	\$1,504.17	HU	36324	71.0	50	NE
	300D0087EG	#300 Reversible Beam Clamp 7/8" EG (Replaces 3000087EG)	\$1,504.17	HU	58849	71.0	50	NE
	3000087PL	#300 Reversible Beam Clamp 7/8"	\$1,103.05	HU	36325	71.0	50	NE
300D0087PL	#300 Reversible Beam Clamp 7/8" (Replaces 3000087PL)	\$1,103.05	HU	58850	71.0	50	NE	
300C	300C3706EG	#300C Retainer Strap 3/8" x 6" EG	\$265.08	HU	33980	11.0	100	NE
	300C3708EG	#300C Retainer Strap 3/8" x 8" EG	\$295.37	HU	33981	14.0	100	NE
	300C3710EG	#300C Retainer Strap 3/8" x 10" EG	\$340.11	HU	33982	18.0	100	NE
	300C3712EG	#300C Retainer Strap 3/8" x 12" EG	\$423.65	HU	33983	22.0	100	NE
	300C3714EG	#300C Retainer Strap 3/8" x 14" EG	\$423.65	HU	33984	25.0	100	NE
	300C5006EG	#300C Retainer Strap 1/2" x 6" EG †	\$265.08	HU	33985	11.0	100	NE
	300C5008EG	#300C Retainer Strap 1/2" x 8" EG †	\$295.37	HU	33986	14.0	100	NE
	300C5010EG	#300C Retainer Strap 1/2" x 10" EG †	\$340.11	HU	33987	18.0	100	NE
	300C5012EG	#300C Retainer Strap 1/2" x 12" EG †	\$423.65	HU	33988	22.0	100	NE
	300C5014EG	#300C Retainer Strap 1/2" x 14" EG	\$423.65	HU	33989	25.0	100	NE