



CAT BEAM ASSEMBLIES- SM

CAT1224SM

3/4" J-Hook assembled to hammer-on 1/8" thru 1/4" flange - side mount



Ordering Information

Region	Part / Article #
North America	CAT1224SM
Latin America	CAT1224SM
Europe/Middle East/Africa	181510
Asia/Australia	CAT1224SM

Features

- cULus® Listed and complies with NEC® and TIA requirements for structured cabling systems.
- Cost-effective alternative to expensive cable tray
- Galvanized finish on J-hooks provide smoother cable pull and greater corrosion resistance.
- Many sizes and designs available to attach to a variety of structures.
- Provides proper support of Category 5e, Category 6a, fiber optic and innerduct
- 3/4" Diameter Loop
- Pregalvanized finish on J-hooks provide smoother cable pull and greater corrosion resistance.

Notes

- For all CADDY® CABLECAT supports, make sure cable sag between fasteners is no more than 12" at midspan. (Actual cable sag will depend on the number of cables in each bundle and the weight of the cable.) To achieve this, locate the supports every 4-5 feet to stay within the 12" sag criterion.

Product Specifications

Package Weight (Imperial)	40 lbs
Patent Number	5,740,994
Standard Packaging Quantity	40
Third Party Certifications	cULus®
Type	Wide Base Cable Support Clips - 3/4" Diameter Loop

Application Photos

**WARNING**

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

WARRANTY

ERICO products are warranted to be free from defects in material and workmanship at the time of shipment. NO OTHER WARRANTY, WHETHER EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), SHALL EXIST IN CONNECTION WITH THE SALE OR USE OF ANY ERICO PRODUCTS. Claims for errors, shortages, defects or nonconformities ascertainable upon inspection must be made in writing within 5 days after Buyer's receipt of products. All other claims must be made in writing to ERICO within 6 months from the date of shipment or transport. Products claimed to be nonconforming or defective must, upon ERICO's prior written approval in accordance with its standard terms and procedures governing returns, promptly be returned to ERICO for inspection. Claims not made as provided above and within the applicable time period will be barred. ERICO shall in no event be responsible if the products have not been stored or used in accordance with its specifications and recommended procedures. ERICO will, at its option, either repair or replace nonconforming or defective products for which it is responsible or return the purchase price to the Buyer. THE FOREGOING STATES BUYER'S EXCLUSIVE REMEDY FOR ANY BREACH OF ERICO WARRANTY AND FOR ANY CLAIM, WHETHER SOUNDING IN CONTRACT, TORT OR NEGLIGENCE, FOR LOSS OR INJURY CAUSED BY THE SALE OR USE OF ANY PRODUCT.

LIMITATION OF LIABILITY

ERICO excludes all liability except such liability that is directly attributable to the willful or gross negligence of ERICO's employees. Should ERICO be held liable its liability shall in no event exceed the total purchase price under the contract. ERICO SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS OF BUSINESS OR PROFITS, DOWNTIME OR DELAY, LABOR, REPAIR OR MATERIAL COSTS OR ANY SIMILAR OR DISSIMILAR CONSEQUENTIAL LOSS OR DAMAGE INCURRED BY BUYER.

Due to a policy of continued product development, specifications are subject to change without notice.

Copyright © 2013 ERICO International Corporation.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.