

Part No.	Description	UPC Code 782856-	Quantity		Weight Per Box (lbs.)	List Price	Per	Prod. Family
			Box	Case				
CD2.5BSS	Conduit clamp with built-in nut; 1-1/4" EMT; 1/4" mounting hole; stainless steel*	12052	100	600	5.00	369.42	HU	ND
CD2B	Conduit clamp with built-in nut; 1" rigid or EMT; 1/4" mounting hole*	12002	100	600	3.64	71.71	HU	ND
CD2B37	Conduit clamp with built-in nut; 1" rigid or EMT; 3/8" mounting hole	34464	100	600	4.77	71.71	HU	ND
CD2BSS	Conduit clamp with built-in nut; 1" rigid or EMT; 1/4" mounting hole; stainless steel*	12060	100	600	4.55	376.40	HU	ND
CD3B	Conduit clamp with built-in nut; 1-1/4" rigid or 1-1/2" EMT; 1/4" mounting hole*	12003	100	600	5.05	84.64	HU	ND
CD3B37	Conduit clamp with built-in nut; 1-1/4" rigid or 1-1/2" EMT; 3/8" mounting hole	34466	100	600	5.23	84.64	HU	ND
CD3BSS	Conduit clamp with built-in nut; 1-1/4" rigid or 1-1/2" EMT; 1/4" mounting hole; stainless steel*	12053	100	600	5.14	385.81	HU	ND
CD4B	Conduit clamp with built-in nut; 1-1/2" rigid; 5/16" mounting hole*	12004	50	300	4.09	103.55	HU	ND
CD4B37	Conduit clamp with built-in nut; 1-1/2" rigid; 3/8" mounting hole	34467	50	300	4.09	103.55	HU	ND
CD4BSS	Conduit clamp with built-in nut; 1-1/2" rigid; 5/16" mounting hole; stainless steel*	12054	50	300	3.86	669.41	HU	ND
CD5B	Conduit clamp with built-in nut; 2" rigid or EMT; 5/16" mounting hole*	12005	50	400	5.45	138.77	HU	ND
CD5B37	Conduit clamp with built-in nut; 2" rigid or EMT; 3/8" mounting hole	34468	50	400	5.45	138.77	HU	ND
CD5BSS	Conduit clamp with built-in nut; 2" rigid or EMT; 5/16" mounting hole; stainless steel*	12055	50	400	5.77	790.73	HU	ND
CD6B	Conduit clamp- 2-1/2" rigid or EMT; 5/16" mounting hole	12006	25	150	3.18	205.17	HU	ND
CD6BSS	Conduit clamp- 2-1/2" rigid or EMT; 5/16" mounting hole; stainless steel	12056	25	150	3.18	1,056.59	HU	ND
CD7B	Conduit clamp- 3" rigid or EMT; 5/16" mounting hole	12007	25	150	3.50	231.80	HU	ND
CD7BSS	Conduit clamp- 3" rigid or EMT; 5/16" mounting hole; stainless steel	12057	25	150	3.64	1,177.99	HU	ND
CD8B	Conduit clamp- 3-1/2" rigid or EMT; 5/16" mounting hole	12008	10	60	1.73	292.40	HU	ND
CD8BSS	Conduit clamp- 3-1/2" rigid or EMT; 5/16" mounting hole; stainless steel	12058	10	60	1.82	1,259.35	HU	ND
CD9B	Conduit clamp- 4" rigid or EMT; 5/16" mounting hole	12009	10	60	2.00	348.72	HU	ND
CD9BSS	Conduit clamp- 4" rigid or EMT; 5/16" mounting hole; stainless steel	12059	10	60	2.05	1,453.38	HU	ND
CER4	NMC and MC/AC cable support	63833	100	100	18.92	76.10	HU	MA
CG4	Cable gripper cable support*	230	100	1000	0.68	41.61	HU	MA
CG4BP	Cable gripper cable support - blister pack*	32598	1	1	2.18	10.90	EA	MA
CHBTC	Box mounting clip	52252	100	1000	1.05	47.70	HU	MA
CJ6IN	Cable support- Non-metallic or metal clad to wood or metal stud	33090	100	800	2.65	80.89	HU	MA
CJ6S	AC or Flexible Cable to Furring strip and hat channel*	50406	100	600	2.25	76.61	HU	MA
CL10000EG	1-5/8" Closure strip, EG	34508	10	500	42.73	411.64	HU	NP
CL10000PS	1-5/8" Closure strip plastic	35195	10	500	8.18	330.76	HU	NP
CM2416M	Retainer Strap Assembly 1/8"-1/4" Flange - 1" conduit - seismic*	51110	50	N/A	4.86	462.60	HU	MA
CM24812M	Retainer Strap Assembly 1/8"-1/4" Flange - 1/2" & 3/4" conduit - seismic*	51100	50	N/A	4.73	456.99	HU	MA
CM24S	Retainer Strap Assembly - seismic- 1/8"-1/4" - 1/4-20 x 3/8" stud*	51010	50	N/A	4.18	426.83	HU	MA
CM5816M	Retainer Strap Assembly- 5/16"-1/4" - 1" conduit*	51330	50	N/A	6.50	503.62	HU	MA
CM58812M	Retainer Strap Assembly- 5/16"-1/4" - 1/2" & 3/4" conduit*	51120	50	N/A	6.36	498.13	HU	MA
CM58S	Retainer Strap Assembly- seismic- 5/16-1/2 - 1/4-20 x 3/8 stud*	51020	50	N/A	5.91	473.60	HU	MA
CM91216M	Retainer Strap Assembly- 9/16-3/4 - 1 conduit*	51150	50	N/A	7.00	525.95	HU	MA
CM912812M	Retainer Strap Assembly- 9/16-3/4 - 1/2 & 3/4 conduit*	51140	50	N/A	6.77	520.57	HU	MA
CM912S	Retainer Strap Assembly- seismic- 9/16-3/4 - 1/4-20 x 3/8 stud*	51030	50	N/A	6.23	489.34	HU	MA
CNB12P	P-Series nail bracket for 3/4 EMT or 1/2 rigid	34262	100	1000	2.59	132.40	HU	MA
CNB812M	M-Series nail bracket for 1/2 or 3/4 conduit	34210	100	600	2.82	122.52	HU	MA
CNB8P	P-Series nail bracket for 1/2 EMT	34258	100	1000	2.45	129.15	HU	MA
CPR21	MSP20 Body spare part kit	46821	1	N/A	1.59	167.88	EA	MA
CPR22	MSP20 Lever spare part kit	46822	1	N/A	0.91	110.75	EA	MA
CPR23	MSP20 H linkage spare part kit	46823	1	N/A	0.11	51.40	EA	MA
CPR24	MSP20 Die spare part kit	46824	1	N/A	0.11	65.63	EA	MA
CPR25	MSP20 Cutter spare part kit	46825	1	N/A	0.23	99.14	EA	MA
CPR28	MSP20 Punch replacement part kit	46828	1	N/A	0.11	19.67	EA	MA
CPR29	MSP20 Grip spare part kit	46829	2	N/A	0.11	3.90	EA	MA
CS16	1" EMT conduit- MC/AC to metal or wood stud for 2-1/8" deep box *	58823	100	600	7.33	53.94	HU	MA
CS812	1/2" and 3/4" EMT conduit- MC/AC to metal or wood stud for 1-1/2" deep box *	32606	100	600	2.55	50.73	HU	MA
CS812D	1/2" and 3/4" EMT conduit- MC/AC to metal or wood stud for 2-1/8" deep box *	32758	100	600	2.82	53.55	HU	MA
CT128TRK	CADDY® CAT TRAX Transition Kit	38267	1	N/A	3.41	173.77	EA	MY
DBM2	Double box mount, wood or metal stud	43927	50	300	2.73	170.81	HU	MA

\* UL® Listed

POA = Call ERICO®