



## Mounting Plate Brackets (Non-Metallic)

MPAL2

Non-Metallic double gang mounting plate



### Ordering Information

Region	Part / Article #
North America	MPAL2
Latin America	MPAL2
Europe/Middle East/Africa	182360
Asia/Australia	MPAL2

### Application Information

- The CADDY® MP Series Mounting Plate allows for the installation of low voltage datacomm and alarm devices into drywall without installation tools. The bracket eliminates the need for electrical boxes on low voltage Class 2 applications. A serrated interlocking system secures the bracket tightly to drywall. The plastic design has no sharp edges and provides the industry with the widest application range of 1/4" to 1-1/4".

### Features

- Double gang
- Eliminates the need for electrical boxes on low voltage class 2 applications
- Fast, easy way to install
- No installation tools required to secure bracket in the drywall opening.
- No sharp metal edges with plastic design
- Only CADDY® provides the industry with the widest application range 1/4" to 1 1/4" wall thickness
- Recessed design helps assure flush mount of device
- Serrated interlocking system secures tightly
- Template dimples on the bracket provide measurement markings for simplified installation

### Notes

- For low voltage Class 2 use only.
- No Load Rating - Positioning Only

### Product Specifications

Standard Packaging Quantity	100
Third Party Certifications	cULus®

### Application Photos

**WARNING**

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

**WARRANTY**

ERICO products are warranted to be free from defects in material and workmanship at the time of shipment. NO OTHER WARRANTY, WHETHER EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), SHALL EXIST IN CONNECTION WITH THE SALE OR USE OF ANY ERICO PRODUCTS. Claims for errors, shortages, defects or nonconformities ascertainable upon inspection must be made in writing within 5 days after Buyer's receipt of products. All other claims must be made in writing to ERICO within 6 months from the date of shipment or transport. Products claimed to be nonconforming or defective must, upon ERICO's prior written approval in accordance with its standard terms and procedures governing returns, promptly be returned to ERICO for inspection. Claims not made as provided above and within the applicable time period will be barred. ERICO shall in no event be responsible if the products have not been stored or used in accordance with its specifications and recommended procedures. ERICO will, at its option, either repair or replace nonconforming or defective products for which it is responsible or return the purchase price to the Buyer. THE FOREGOING STATES BUYER'S EXCLUSIVE REMEDY FOR ANY BREACH OF ERICO WARRANTY AND FOR ANY CLAIM, WHETHER SOUNDING IN CONTRACT, TORT OR NEGLIGENCE, FOR LOSS OR INJURY CAUSED BY THE SALE OR USE OF ANY PRODUCT.

**LIMITATION OF LIABILITY**

ERICO excludes all liability except such liability that is directly attributable to the willful or gross negligence of ERICO's employees. Should ERICO be held liable its liability shall in no event exceed the total purchase price under the contract. ERICO SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS OF BUSINESS OR PROFITS, DOWNTIME OR DELAY, LABOR, REPAIR OR MATERIAL COSTS OR ANY SIMILAR OR DISSIMILAR CONSEQUENTIAL LOSS OR DAMAGE INCURRED BY BUYER.

Due to a policy of continued product development, specifications are subject to change without notice.

Copyright © 2013 ERICO International Corporation.

CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

**ERICO®**