

RIGHT ANGLE PIPE SUPPORT RA

Malleable Iron, HD

- Size Range: 3/8" – 4"
- Surface Finish: Hot-dip galvanized
- Structural attachments of pipe sizes from 3/8" - 4" to beams with up to 3/4" flange thickness



Part Number	Nominal Pipe Size	A	Max. Rec. Load (lbs)
RA0037HD	3/8"	3/4"	200
RA0050HD	1/2"	3/4"	250
RA0075HD	3/4"	3/4"	300
RA0100HD	1"	3/4"	400
RA0125HD	1-1/4"	3/4"	400
RA0150HD	1-1/2"	3/4"	500
RA0200HD	2"	3/4"	600
RA0250HD	2-1/2"	3/4"	700
RA0300HD	3"	3/4"	800
RA0350HD	3-1/2"	3/4"	900
RA0400HD	4"	3/4"	1000

