



CADDY® PYRAMID 150

CADDY® PYRAMID 150 Pipe & Equipment Support from ERICO® provides an easy method for supporting up to 150 lb loads of pipe, conduit and equipment. CADDY PYRAMID dramatically reduces installation time by replacing other labor-intensive support methods such as wood blocks, straps and clips.

Features

- Supports up to 150 lb loads
- Electro-galvanized (EG) finish on top plate for added corrosion protection
- Polyethylene closed-cell foam and 14-gauge steel construction
- Absorbs shock and vibration
- Protects roof membrane
- Has six 3/8"-16 threaded inserts with captive nuts that allows the product to be used with standard pipe clamps and accessories.
- Large 16" x 12" footprint distributes load more evenly than alternative methods
- With or without strut. Strut length is 16".



Applications

Supports equipment or multiple runs of pipe and conduit and provides for numerous mounting options and clamping positions.

More Information

Part No.	Max Working Load (lb)	Height (in)	Threads	Finish	Strut Included?
RPS150T1	150	3-3/16	3/8"-16	EG	No
RPS150T2	150	4	3/8"-16	EG	Yes

Product available with other thread configurations and surface finishes.

WARNING

ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at www.erico.com and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

WARRANTY

ERICO products are warranted to be free from defects in material and workmanship at the time of shipment. NO OTHER WARRANTY, WHETHER EXPRESS OR IMPLIED (INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE), SHALL EXIST IN CONNECTION WITH THE SALE OR USE OF ANY ERICO PRODUCTS. Claims for errors, shortages, defects or nonconformities ascertainable upon inspection must be made in writing within 5 days after Buyer's receipt of products. All other claims must be made in writing to ERICO within 6 months from the date of shipment or transport. Products claimed to be nonconforming or defective must, upon ERICO's prior written approval in accordance with its standard terms and procedures governing returns, promptly be returned to ERICO for inspection. Claims not made as provided above and within the applicable time period will be barred. ERICO shall in no event be responsible if the products have not been stored or used in accordance with its specifications and recommended procedures. ERICO will, at its option, either repair or replace nonconforming or defective products for which it is responsible or return the purchase price to the Buyer. THE FOREGOING STATES BUYER'S EXCLUSIVE REMEDY FOR ANY BREACH OF ERICO WARRANTY AND FOR ANY CLAIM, WHETHER SOUNDING IN CONTRACT, TORT OR NEGLIGENCE, FOR LOSS OR INJURY CAUSED BY THE SALE OR USE OF ANY PRODUCT.

LIMITATION OF LIABILITY

ERICO excludes all liability except such liability that is directly attributable to the willful or gross negligence of ERICO's employees. Should ERICO be held liable its liability shall in no event exceed the total purchase price under the contract. ERICO SHALL IN NO EVENT BE RESPONSIBLE FOR ANY LOSS OF BUSINESS OR PROFITS, DOWNTIME OR DELAY, LABOR, REPAIR OR MATERIAL COSTS OR ANY SIMILAR OR DISSIMILAR CONSEQUENTIAL LOSS OR DAMAGE INCURRED BY BUYER.

Due to a policy of continued product development, specifications are subject to change without notice.

Copyright © 2013 ERICO International Corporation.
CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

