


ISO Low Voltage Insulators, Imperial Thread – ISO2-18-38 (559683)



- Great stability of electrical and mechanical parameters
- High resistance to leakage current
- UL® Recognized in E125470 and evaluated for dielectric withstand rating of 1,500 VAC/DC
- Halogen free
- RoHS compliant



Part Number	ISO2-18-38
Article Number	559683
Material	Glass Fibre Reinforced Polyester Steel
Finish	Electrogalvanized
Working Temperature	-40 to 266 °F
Flammability Rating	UL® 94V-0
Height (H)	2.175"
Hex Width (W)	2 1/2"
Depth (D)	2.89"
Thread Size (TS)	3/8 UNC
Thread Depth (TD)	5/8"
Diameter (Ø)	2.14"
Insulation Voltage	2,500 VAC
Static Load 1 (F1)	3,000 lb
Static Load 2 (F2)	1,300 lb
Unit Weight	0.629 lb
Certifications	CSA-Comp cURus

Part Number	ISO2-18-38
	RoHS
Standard Packaging Quantity	25 pc
UPC	78285658325

Creepage and clearance distances need to be in accordance with the relevant application standard.

UL, UR, cUL, cUR, cULus and cURus are registered certification marks of UL LLC.

WARNING

Pentair products shall be installed and used only as indicated in Pentair's product instruction sheets and training materials. Instruction sheets are available at erico.pentair.com and from your Pentair customer service representative. Improper installation, misuse, misapplication or other failure to completely follow Pentair's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2017 Pentair All rights reserved

Pentair, CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH and LENTON are owned by Pentair or its global affiliates.

All other trademarks are the property of their respective owners. Pentair reserves the right to change specifications without prior notice.