

CADDY® PYRAMID Pipe & Equipment Supports



CADDY® PYRAMID 300:

- ▲ Same design, steel plate and finish choices as CADDY® PYRAMID 150
- ▲ Cross-linked polyethylene closed-cell foam supports up to 300 lbs; 14-gauge steel top plate

Part Number	Max. Working Load (lbs)	H (in)	Threads	Strut Included?	Finish
RPS300T1	300	3-3/16	3/8 - 16	No	EG
RPS300T2	300	4	3/8 - 16	Yes	EG



CADDY® PYRAMID 600:

- ▲ Consists of two CADDY PYRAMID 300 bases attached with a length of strut to support 600 lb loads each
- ▲ Footprint is 32" x 12" (24" x 16" optional with cutting of strut) for more even load distribution
- ▲ Has twelve 3/8 - 16 threaded inserts

Part Number	Max. Working Load (lbs)	H (in)	Threads	Strut Included?	Finish
RPS600T2	600	4	3/8 - 16	Yes	EG

CADDY PYRAMID Accessories



P110000EG



CADDY® PYRAMID Column Supports:

- ▲ Attaches directly to strut
- ▲ For added flexibility, strut can be cut to length on-site as required for the application



RPSCSEG



Part Number	Description	Finish	Packing Unit
RPSCSEG	Strut-to-strut post base for RPS 50/150/300	EG	1
P110000EG	Strut post base for RPS 150/300	EG	1

