

SPLICE KITS

"proSplice™" UL Listed Splice Kits

- Direct burial splice enclosure kit.
- No heat shrink tubing or epoxy needed.
- Fast, clean, reusable.
- A twist of the wrist and a water tight mechanical connection is completed.

- Rated to 600V.
- UL listed.
- BellCore audited.
- CSA.
- Made in U.S.A.



- **SK1** - 14-10 AWG UF Cu/Sol/Str. Includes 4 butt splices and grommets.
- **SKS** - proSplice shells only.
- **SK1-FD** - 10 SK1 in counter display



- **SK3** - 6-1 AWG USE Cu/Al Wire OD size .32" - .53" Includes connector and grommets.
- **SK3-FD** - 10 SK3 in counter display



- **SK1C** - 14-10 AWG UF Cu/Sol/Str. Includes classic SK830 Quad connector and grommets.
- **SK1C-FD** - 10 SK1C in counter display



- **SK4** - 1/0 USE to 350 MCM Wire OD size .180" - .320" Includes grommets. Connector not included.
- **SK4-FD** - 10 SK4 in counter display



- **SK2** - 12-6 AWG USE Cu/Al Wire OD size .180" - .320" Includes connector and grommets.
- **SK2-FD** - 10 SK2 in counter display



- **PK1** - 2-6 pair buried phone wire, coaxial RG6 & RG59. Connector not included.
- **PK1-FD** - 10 PK1 in counter display

Great for use with aquatic systems, fountains, landscaping, ponds, etc.



"proSplice™" Extenders

- Increases cavity size of all proSplice kits. Allows for larger coax connectors and additional phone wires to be terminated. Available in 4", 6", 8" and 10" lengths.
- Extenders come with SKS shells. Grommets not included.
- Catalog #'s are: EXT4, EXT6, EXT8, EXT10.
- UL listed.
- BellCore audited.
- CSA.
- Made in U.S.A.



SKUF

- Direct burial splice enclosure kit for #14/2 and #12/2 UF wire.
- Includes grommets and 3-butt splice connectors.
- Made in U.S.A.

SKU1

- Direct burial splice enclosure kit for #12 - #10 AWG wire.
- Includes grommets and 1-butt splice connectors.
- Made in U.S.A.

SKU2

- Direct burial splice enclosure kit for #8 - #2 AWG wire.
- For use with compression connector.
- Includes grommets.
- Compression connector not included.
- Made in U.S.A.



"proSplice™" Taps

- 3 or 4 wire taps with no tape or heat shrink needed.
- T-splice with single in and double out.
- Four wire splice with double in and double out.
- Dead-end splice available.
- UL listed.
- BellCore audited.
- CSA.
- Made in U.S.A.



SKCX

- Direct burial splice enclosure kit for coaxial RG6, RG11, RG59.
- Dimensions 6" long X 3/4" diameter
- Includes grommets.
- UL listed.
- Made in U.S.A.
- **SKCX-FD** - 10 SKCX in counter display

The ETCON SKCX splice kit allows the technician to complete a direct burial splice for RG6, RG11 and RG59 wires, and 2-4 pair phone wires.

The splice enclosure is quick and easy to install. No special tools are required, no mixing of compounds, laborious taping, messy gels, or dangerous, "heat shrinking" flames. The splice enclosures are completely re-enterable for visual inspection. The splice enclosure is manufactured with an engineering grade polymer-based outer housing that resists moisture, petroleum-based products, chemicals and rodents. The SKCX provides additional pullout strength for added splice quality.

FREE Display Case

See back cover for details

