


# WINDPOINTE® SERIES

## Fan Motor Assembly

MA7500 Series	
Fan Motor Assembly (188 x 25)	Available Finishes
	MA7500AB – Antique Brass*
	MA7500MW – Matte White <b>(Damp)</b>
	MA7500OB – Oil-Rubbed Bronze
	MA7500PW – Pewter
	MA7500RS – Rust* <b>(Damp)</b>

\*220 VAC, 50 Hz export version available in this finish.

MA7500 Airflow / Energy Efficiency Info (120V)					
Fan Speed	Max RPM	CFM	CFM / Watts	Amps	Watts
High	110	3468	82	0.37	42
Med	97	3010	88	0.33	34
Low	63	1743	106	0.23	17

Blade sweep varies depending on blade selection, see chart on page 79

### INSTALLATION REQUIREMENTS:

Fan must be attached to a securely anchored electrical junction box capable of withstanding a load of at least 50 lbs.

### ELECTRICAL REQUIREMENTS:

Requires a grounded electrical supply line of 120 volts AC, 60 Hz, 15 amp circuit.

### FAN SPEEDS / BLADES:

3 fan speeds with pull chain and reversing switch (on switch cup housing). Speeds will vary depending on blade size and type. All blade sets are sold separately. See our catalog or visit [www.fanimation.com](http://www.fanimation.com) for available blade options.

### CONTROL OPTIONS:

Optional CW1, CW1SW, CW2, CW5 and CWRL4 wall controls and CRL4WH and CRL8TS remote controls (with receiver units) are available—sold separately. Instructions are provided with each control.

### LIGHTING OPTIONS:

Optional lighting fitters and light kits are available. See our catalog or visit [www.fanimation.com](http://www.fanimation.com) for lighting options.

### DOWNROD OPTIONS:

Fan comes with 1" dia. x 4.5" long downrod. Optional downrods available in 12", 18", 24", 36", 48", 60", and 72" lengths. A downrod coupler is available for installations requiring a downrod longer than 72". Fan can be mounted on a sloped ceiling up to 30°. Optional close-to-ceiling kit is available as well-sold separately. Call your local dealer for more information.