

GGU Fast-Acting Midget Fuses

125 volt AC rated GGU fuses have midget fuse dimensions (1-1/2" long x 13/32" diameter). 20A-30A ratings have ceramic bodies, allowing use in higher ambient temperature conditions than other similar fuses. (Not for Branch Circuit Protection).

Features/Benefits:

- Glass body on 1-15A makes status of fusible element clearly visible
- Ceramic body on 20-30A allows use in higher temperature applications
- Medium lag for protection of circuits up to 30A and 125VAC
- Can be used with UltraSafe™ fuse holders (1-30A)
- 1 1/2" x 13/32" (10mm x 38mm) dimensions

Highlights:

- Fast-acting

Catalog Numbers (amps)

GGU1
GGU2
GGU3
GGU4
GGU5
GGU8
GGU10
GGU15
GGU20
GGU30

Recommended Fuse Blocks for Midget (10x38mm) Fuses

Number of Poles	UltraSafe™ Indicating Fuse Holder	Catalog Number		
		Screw Connector	Pressure Plate Connector	Copper Box Connector
Adder		30310	30320	30350
1	USM1I	30311	30321	30351
2	USM2I	30312	30322	30352
3	USM3I	30313	30323	30353
3	USFM10I			



Ratings:

Volts : 125VAC
Amps : 1 to 30A
I.R. : 10kA I.R.

Approvals:

- UL Listed 1-15A
- UL Recognized 20-30A

