



Actual

**Catalog Number:** 20HPS  
**Product ID:** 7TAH006110R0003  
**UPC Number:** 78378620028  
**EAN Number:** 05414363138808  
**Status:** Active

Type HPS - Split-Bolt Connector with Spacer, Conductor Range for Equal Main and Tap AC-SR 1/0-6, Conductor Range for Equal Main and Tap 2/0 Str-6 Str, Min Tap with One Max Main 6 Sol, Tin Plated

- Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of electrolytic copper.
- Splicing, tapping or terminating conductors in power and grounding electrical connection.

### North American Specifications (UNSPSC)

UNSPSC	39121408 Mechanical connectors
IGCC	4541 Mechanical connectors
Brand Name	Blackburn
Type	Split-Bolt
Special Features	Bolt and pressure bar of copper alloy, completely tin plated for corrosion resistance. Contoured spacer of electrolytic copper.
Application	Splicing, tapping or terminating conductors in power and grounding electrical connection.
Standard	UL E9809
Material	Copper Alloy
Finish	Electro Tin-Plated

### European Specifications (ETIM)

ETIM	EC000491 Earth terminal clamp
Suitable for	Round conductor
Material	Copper

### Packaging

Inner Quantity	25
Inner Dimensions (inches)	7.375x5.5x4
Outer Quantity	150
Outer Dimensions (inches)	11.7x11x8
Weight Uom	32.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000072

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)