



Representative

Catalog Number: IKL66
Product ID: 7TAA267180R0042
UPC Number: 78378605035
EAN Number: 05415022348880
Status: Active

Aluminum 5-1/2 inch Service Entrance Compression Splice for Wire Range - End A: 4/0 AS-CR, 4/0 Str., Yellow, End B: 1/0 ASCR, 1/0 Str., Yellow, Die: 840

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Blackburn
Type	Service Entrance Splices
Special Features	Pre-insulated for fast, easy installation of large home or commercial service entrances. Concave polyethylene end caps seal out dirt, but are easily pierced when inserting conductor.
Application	For Combinations of Aluminum-to-Aluminum and Aluminum-to-Copper Conductors. Use as a low tension reducing sleeve for Insulated Conductor.
Standard	RUS Listed. Passes the Requirements of ANSI C119.4
Size	5-1/2 inch
Connection	Crimp/ Compression
Conductor Range	End A: 4/0 ASCR, 4/0 Stranded, End B: 1/0 ASCR, 1/0 Stranded.
Number Of Conductors	2
Material	Aluminum
Insulation	Yes
Mounting	None
Environmental Conditions	All Seasons / Conditions

Packaging

Inner Quantity	25
Inner Dimensions (inches)	7.25x6.5x4
Outer Quantity	100
Outer Dimensions (inches)	14x9.625x7.75
Weight Uom	19.75 lbs. per 100

Documents / Support Tools

SDS US 1	sds-00042-tb2
Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com