

Fluke CLKTO IR Window for Indoor Medium Voltage

Infrared Windows – Fluke CLKTO IR window helps increase the safety of your personnel and reduces cost of predictive maintenance in compliance with indoor switchgear code.

This product is discontinued or reclassified



Specs

Specifications

Optic data	3460611 FLK-075-CLKTO	
Crystal insert diameter	75 mm (2.96 in)	
Viewing aperture diameter	68 mm (2.7 in)	
Viewing aperture area	3632 mm ² (5.63 sq in)	
Thickness	2 mm (0.08 in)	
Shortwave IR, Midwave IR, Longwave IR, Ultraviolet (UV) capable	Yes	
Visual and fusion capable	Yes	
Maximum temperature	Gaskets	250 °C (482 °F)
	Body	659 °C (1219 °F)
	Optic	1400 °C (2552 °F)
Viewing pane	150 °C (302 °F)	
Gaskets	Low smoke and fume (LSF) compliant silicone	
Pull-out strength	Up to 630 kg (1388 lb)	
Warranty	Lifetime replacement against manufacturing	