

Molded Case Circuit Breakers

Q-Line Circuit Breakers

Cable-in Cable-out (lug-lug)
240V Class

Section 6

TQD 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number ^{1,2} |
|------------|---------------|-----------------------------|-------------------------------|
| 2 | 100 | 10kA | TQD22100WL |
| 2 | 125 | 10kA | TQD22125WL |
| 2 | 150 | 10kA | TQD22150WL |
| 2 | 175 | 10kA | TQD22175WL |
| 2 | 200 | 10kA | TQD22200WL |
| 2 | 225 | 10kA | TQD22225WL |
| 3 | 100 | 10kA | TQD32100WL |
| 3 | 125 | 10kA | TQD32125WL |
| 3 | 150 | 10kA | TQD32150WL |
| 3 | 175 | 10kA | TQD32175WL |
| 3 | 200 | 10kA | TQD32200WL |
| 3 | 225 | 10kA | TQD32225WL |



TJD432400WL

TQD 240 Vac, Internal Common Trip with Factory Installed 120 Vac Shunt Trip³

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number ^{1,2} |
|------------|---------------|-----------------------------|-------------------------------|
| 3 | 125 | 10kA | TQD32125ST1 |
| 3 | 150 | 10kA | TQD32150ST1 |
| 3 | 175 | 10kA | TQD32175ST1 |
| 3 | 200 | 10kA | TQD32200ST1 |
| 3 | 225 | 10kA | TQD32225ST1 |

THQD 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number ^{1,2} |
|------------|---------------|-----------------------------|-------------------------------|
| 2 | 100 | 22kA | THQD22100WL |
| 2 | 125 | 22kA | THQD22125WL |
| 2 | 150 | 22kA | THQD22150WL |
| 2 | 175 | 22kA | THQD22175WL |
| 2 | 200 | 22kA | THQD22200WL |
| 2 | 225 | 22kA | THQD22225WL |
| 3 | 100 | 22kA | THQD32100WL |
| 3 | 125 | 22kA | THQD32125WL |
| 3 | 150 | 22kA | THQD32150WL |
| 3 | 175 | 22kA | THQD32175WL |
| 3 | 200 | 22kA | THQD32200WL |
| 3 | 225 | 22kA | THQD32225WL |

TJD 240 Vac, Internal Common Trip

| # of Poles | Ampere Rating | 240 Vac Interrupting Rating | Product Number ^{1,2} |
|------------|------------------------|-----------------------------|-------------------------------|
| 2 | 250 | 22kA | TJD422250WL |
| 2 | 300 | 22kA | TJD422300WL |
| 2 | 350 | 22kA | TJD422350WL |
| 2 | 400 | 22kA | TJD422400WL |
| 2 | 400 Molded Case Switch | 22kA | TJD422Y400 |
| 3 | 250 | 22kA | TJD432250WL ⁴ |
| 3 | 300 | 22kA | TJD432300WL ⁴ |
| 3 | 350 | 22kA | TJD432350WL ⁴ |
| 3 | 400 | 22kA | TJD432400WL ⁴ |
| 3 | 400 Molded Case Switch | 22kA | TJD432Y400 ⁴ |

¹Refer to table on page 6-106 for lug and wire range data.

²Includes line and load lugs. For optional configurations see page 6-3.

³For additional shunt trip options see page 6-41.

⁴TJD uses same accessories as J600 line. TJD not listed HACR.

UL listed HACR (heating, air conditioning and refrigeration).

