

Specialty Control Devices

Limit Switches

Section 11

CR115A

Vane-Operated Limit Switches

CR115A Standard Forms

Contact Configuration	Orientation	Lead Length	Product Number	List Price GO-10G6
1 NO	Front	3 ft.	CR115A11 ¹	\$244.00
1 NC	Front	3 ft.	CR115A12 ¹	\$244.00
1 NO	Top	3 ft.	CR115A15 ¹	\$244.00
1 NC	Top	3 ft.	CR115A16 ¹	\$244.00
1 NO	Front	12 ft.	CR115A11AC	\$260.00
1 NC	Front	12 ft.	CR115A12AC	\$260.00
1 NO	Top	12 ft.	CR115A15AC	\$260.00
1 NC	Top	12 ft.	CR115A16AC	\$260.00

¹UL listed for Types 3, 3R, 4, 4X, 12, and 13 locations; and for Division 2 Types 7 and 9 hazardous locations

CR115A Standard Forms with Three-Foot Plug Connector and Watertight Bushing²

Contact Configuration	Orientation	Lead Length	Product Number	List Price GO-10G6
1 NO	Front	3 ft.	CR115A26	\$350.00
1 NO	Top	3 ft.	CR115A27	\$350.00

²Switch leads have a male connector for use with female receptacles such as: CAM-LOK E2004-504 (with 3/4-inch pipe thread), E2004-505 (with 1/2-inch pipe thread) or equivalent.

CR115A General Purpose Forms

Contact Configuration	Orientation	Lead Length	Product Number	List Price GO-10G6
1 NO	Front	3 ft.	CR115A30	\$178.00
1 NC	Front	3 ft.	CR115A35	\$178.00
1 NO	Front	12 ft.	CR115A30AC	\$194.00
1 NC	Front	12 ft.	CR115A35AC	\$194.00

CR115A Corrosion Resistant Forms

Contact Configuration	Orientation	Lead Length	Product Number	List Price GO-10G6
1 NO	Front	3 ft.	CR115A38 ³	\$231.00
1 NO	Front	3 ft.	CR115A38AM ⁴	\$231.00
1 NO	Front	12 ft.	CR115A38AC	\$246.00

³Has stainless steel hardware.

⁴Two-position mounting plate.

