

# Low Voltage Power & Insulated Case Circuit Breakers Section 8

## WavePro Low Voltage Power Circuit Breakers

### WavePro Breaker Power+ and MicroVersaTrip™ Plus/PM Rating Plugs

Breaker Frame Size (Amps)	Current Sensor (Amps)	Rating Plug (Amps)	EntelliGuard™ TU	Power+ Rating Plug w/o GF	Power+ Rating Plug with GF	Power+ Rating Plug with Defeatable GF	MicroVersaTrip™ Plus/PM Rating Plug	
800	150	60	GTP0060U0101	N/A	N/A	N/A	TR1B60	
		80	GTP0080U0101	TR1C80	TR1C80GF	TR1C80GFD	TR1B80	
		100	GTP0100U0103	TR1C100	TR1C100GF	TR1C100GFD	TR1B100	
		125	GTP0125U0103	TR1C125	TR1C125GF	TR1C125GFD	TR1B125	
		150	GTP0150U0104	TR1C150	TR1C150GF	TR1C150GFD	TR1B150	
	4000	150	GTP0150U0104	N/A	N/A	N/A	TR4B150	
		200	GTP0200U0204	TR4C200	TR4C200GF	TR4C200GFD	TR4B200	
		225	GTP0225U0306	TR4C225	TR4C225GF	TR4C225GFD	TR4B225	
		250	GTP0250U0407	TR4C250	TR4C250GF	TR4C250GFD	TR4B250	
		300	GTP0300U0408	TR4C300	TR4C300GF	TR4C300GFD	TR4B300	
		400	GTP0400U0410	TR4C400	TR4C400GF	TR4C400GFD	TR4B400	
	800	300	GTP0300U0408	N/A	N/A	N/A	TR8B300	
		400	GTP0400U0410	TR8C400	TR8C400GF	TR8C400GFD	TR8B400	
		450	GTP0450U0612	N/A	N/A	N/A	TR8B450	
		500	GTP0500U0613	TR8C500	TR8C500GF	TR8C500GFD	TR8B500	
		600	GTP0600U0616	TR8C600	TR8C600GF	TR8C600GFD	TR8B600	
		700	GTP0700U0816	TR8C700	TR8C700GF	TR8C700GFD	TR8B700	
		800	GTP0800U0820	TR8C800	TR8C800GF	TR8C800GFD	TR8B800	
	1600	800	300	GTP0300U0408	N/A	N/A	N/A	TR8B300
			400	GTP0400U0410	TR8C400	TR8C400GF	TR8C400GFD	TR8B400
			450	GTP0450U0612	N/A	N/A	N/A	TR8B450
500			GTP0500U0613	TR8C500	TR8C500GF	TR8C500GFD	TR8B500	
600			GTP0600U0616	TR8C600	TR8C600GF	TR8C600GFD	TR8B600	
700			GTP0700U0816	TR8C700	TR8C700GF	TR8C700GFD	TR8B700	
800			GTP0800U0820	TR8C800	TR8C800GF	TR8C800GFD	TR8B800	
1600		600	GTP0600U0616	N/A	N/A	N/A	TR16B600	
		800	GTP0800U0820	TR16C800	TR16C800GF	TR16C800GFD	TR16B800	
		1000	GTP1000U1025	TR16C1000	TR16C1000GF	TR16C1000GFD	TR16B1000	
		1100	GTP1100U1225	N/A	N/A	N/A	TR16B1100	
		1200	GTP1200U1232	TR16C1200	TR16C1200GF	TR16C1200GFD	TR16B1200	
		1600	GTP1600U1640	TR16C1600	TR16C1600GF	TR16C1600GFD	TR16B1600	
2000	2000	750	GTP0750U0820	N/A	N/A	N/A	TR20B750	
		800	GTP0800U0820	N/A	N/A	N/A	TR20B800	
		1000	GTP1000U1025	TR20C1000	TR20C1000GF	TR20C1000GFD	TR20B1000	
		1200	GTP1200U1232	TR20C1200	TR20C1200GF	TR20C1200GFD	TR20B1200	
		1500	GTP1500U1640	N/A	N/A	N/A	TR20B1500	
		1600	GTP1600U1640	TR20C1600	TR20C1600GF	TR20C1600GFD	TR20B1600	
		2000	GTP2000U2050	TR20C2000	TR20C2000GF	TR20C2000GFD	TR20B2000	
3200	3200	1200	GTP1200U1232	TR32C1200	TR32C1200GF	TR32C1200GFD	TR32B1200	
		1600	GTP1600U1640	TR32C1600	TR32C1600GF	TR32C1600GFD	TR32B1600	
		2400	GTP2400U2564	TR32C2400	TR32C2400GF	TR32C2400GFD	TR32B2400	
		3200	GTP3200U3264	TR32C3200	TR32C3200GF	TR32C3200GFD	TR32B3200	
4000	4000	1600	GTP1600U1640	TR40C1600	TR40C1600GF	TR40C1600GFD	TR40B1600	
		2000	GTP2000U2050	TR40C2000	TR40C2000GF	TR40C2000GFD	TR40B2000	
		2500	GTP2500U2564	TR40C2500	TR40C2500GF	TR40C2500GFD	TR40B2500	
		3000	GTP3000U3064	TR40C3000	TR40C3000GF	TR40C3000GFD	TR40B3000	
		3600	GTP3600U4064	N/A	N/A	N/A	TR40B3600	
5000	5000	4000	GTP4000U4064	TR40C4000	TR40C4000GF	TR40C4000GFD	TR40B4000	
		3200	GTP3200U3264	N/A	N/A	N/A	TR50B3200	
		5000	GTP5000U5064	N/A	N/A	N/A	TR50B5000	



# Low Voltage Power & Insulated Case Circuit Breakers Section 8

## Power Break™ II Circuit Breakers

Enhanced MicroVersaTrip™, Rating Plug Selection

### Power Break™ II Rating Plug Selection

Frame Size (Amperes)	Sensor Rating (Amperes)	Current Rating (Amperes)	Power+ Trip Unit Standard Rating Plugs	Power+ Trip Unit Ground Fault Rating Plugs	Enhanced MicroVersaTrip™ Plus and Enhanced MicroVersaTrip™ PM Trip Unit Rating Plugs		EntelliGuard™ TU Trip Unit Rating Plugs
					MicroVersaTrip™ Plus	MicroVersaTrip™ PM	
800	200	100	TR2C100	TR2C100GF	TR2B100	GTP0100U0103	
		150	TR2C150	TR2C150GF	TR2B150	GTP0150U0104	
		200	TR2C200	TR2C200GF	TR2B200	GTP0200U0204	
	400	150	-	-	TR4B150	GTP0150U0104	
		200	TR4C200	TR4C200GF	TR4B200	GTP0200U0204	
		225	TR4C225	TR4C225GF	TR4B225	GTP0225U0306	
		250	TR4C250	TR4C250GF	TR4B250	GTP0250U0407	
		300	TR4C300	TR4C300GF	TR4B300	GTP0300U0408	
		400	TR4C400	TR4C400GF	TR4B400	GTP0400U0410	
800-1600	800	300	-	-	TR8B300	GTP0300U0408	
		400	TR8C400	TR8C400GF	TR8B400	GTP0400U0410	
		450	TR8C450	TR8C450GF	TR8B450	GTP0450U0612	
		500	TR8C500	TR8C500GF	TR8B500	GTP0500U0613	
		600	TR8C600	TR8C600GF	TR8B600	GTP0600U0616	
		700	TR8C700	TR8C700GF	TR8B700	GTP0700U0816	
		800	TR8C800	TR8C800GF	TR8B800	GTP0800U0820	
		400	-	-	TR10B400	GTP0400U0410	
		600	TR10C600	TR10C600GF	TR10B600	GTP0600U0616	
1600	1000	800	TR10C800	TR10C800GF	TR10B800	GTP0800U0820	
		1000	TR10C1000	TR10C1000GF	TR10B1000	GTP1000U1025	
		600	-	-	TR16B600	GTP0600U0616	
	1600	800	TR16C800	TR16C800GF	TR16B800	GTP0800U0820	
		1000	TR16C1000	TR16C1000GF	TR16B1000	GTP1000U1025	
		1100	TR16C1100	TR16C1100GF	TR16B1100	GTP1100U1225	
		1200	TR16C1200	TR16C1200GF	TR16B1200	GTP1200U1232	
		1600	TR16C1600	TR16C1600GF	TR16B1600	GTP1600U1640	
		750	-	-	TR20B750	GTP0750U0820	
2000	2000	800	-	-	TR20B800	GTP0800U0820	
		1000	TR20C1000	TR20C1000GF	TR20B1000	GTP1000U1025	
		1200	TR20C1200	TR20C1200GF	TR20B1200	GTP1200U1232	
		1500	TR20C1500	TR20C1500GF	TR20B1500	GTP1500U1640	
		1600	TR20C1600	TR20C1600GF	TR20B1600	GTP1600U1640	
		2000	TR20C2000	TR20C2000GF	TR20B2000	GTP2000U2050	
		400	-	-	TR10B400	GTP0400U0410	
		600	TR10C600	TR10C600GF	TR10B600	GTP0600U0616	
		800	TR10C800	TR10C800GF	TR10B800	GTP0800U0820	
2500	2000	1000	TR10C1000	TR10C1000GF	TR10B1000	GTP1000U1025	
		750	-	-	TR20B750	GTP0750U0820	
		800	-	-	TR20B800	GTP0800U0820	
		1000	TR20C1000	TR20C1000GF	TR20B1000	GTP1000U1025	
		1200	TR20C1200	TR20C1200GF	TR20B1200	GTP1200U1232	
		1500	TR20C1500	TR20C1500GF	TR20B1500	GTP1500U1640	
		1600	TR20C1600	TR20C1600GF	TR20B1600	GTP1600U1640	
		2000	TR20C2000	TR20C2000GF	TR20B2000	GTP2000U2050	
		1600	TR25C1600	TR25C1600GF	TR25B1600	GTP1600U1640	
3000	2500	2000	TR25C2000	TR25C2000GF	TR25B2000	GTP2000U2050	
		2500	TR25C2500	TR25C2500GF	TR25B2500	GTP2500U2564	
		1200	TR30C1200	TR30C1200GF	TR30B1200	GTP1200U1232	
		1600	TR30C1600	TR30C1600GF	TR30B1600	GTP1600U1640	
		2000	TR30C2000	TR30C2000GF	TR30B2000	GTP2000U2050	
		2500	TR30C2500	TR30C2500GF	TR30B2500	GTP2500U2564	
		3000	TR30C3000	TR30C3000GF	TR30B3000	GTP3000U3064	
		1600	TR40C1600	TR40C1600GF	TR40B1600	GTP1600U1640	
		2000	TR40C2000	TR40C2000GF	TR40B2000	GTP2000U2050	
4000	4000	2500	TR40C2500	TR40C2500GF	TR40B2500	GTP2500U2564	
		3000	TR40C3000	TR40C3000GF	TR40B3000	GTP3000U3064	
		3600	TR40C3600	TR40C3600GF	TR40B3600	GTP3600U4064	
		4000	TR40C4000	TR40C4000GF	TR40B4000	GTP4000U4064	



MicroVersaTrip™ and MicroVersaTrip™ PM Rating Plug



Power+ Trip Target Module



EntelliGuard™ TU Rating Plug

### Power+ Target Module

Power+ trip units are designed to accept an optional field-installable target module. The target module indicates long-time pickup, battery status, trip unit health status, and whether a breaker trip was caused by an overload, a short circuit or a ground fault. Target modules are available with or without ground fault indication.

L/ST/1	Trip Indicator		Product Number
	Ground Fault		
-	-	-	TARGET00
•	•	-	TARGET01
•	•	•	TARGET02

